



Abrazadera 1.5TC 304SS

Código: 306000

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Abrazadera 1.5TC 304SS

Producto publicado con base en la ficha vigente del proveedor Sterlitech.

SKU	Nombre proveedor	Fabricante	Categoría proveedor	Fuente
306000	Clamp 1.5TC 304SS	Advantec	Portafiltros /// Pressure Portafiltros /// Large Portafiltros	Ficha proveedor

Especificaciones técnicas

SKU Sterlitech	306000
Ficha del fabricante	Clamp 1.5TC 304SS
URL fuente	

Tabla fuente 1

	KS 90 KS 90 ST	KS 142 KS 142 ST	KS 293 KS 293 ST	KS 90 UH	KS 142 UH	KS 293 UH	KST 47	KST 90	KST 142
Tamaño de filtro (mm)	90	142	293	90	142	293	47	90	142
Body	304 or 316 Acero inoxidable	304 or 316 Acero inoxidable	304 or 316 Acero inoxidable	304 Acero inoxidable	304 Acero inoxidable	304 Acero inoxidable	304 SS	304 or 316 Acero inoxidable	304 or 316 Acero inoxidable
O-ring & Gasket	Silicone and PTFE	Silicone and PTFE	Silicone and PTFE	Silicone	Silicone	Silicone	Silicone and PTFE	Silicone and PTFE	Silicone and PTFE
Inlet/Outlet	¾" NPTF and NPTM to 3/8" hose barb (ST Models: 1.5" Sanitary fitting to 14.3 mm hose barb)	¾" NPTF and NPTM to 3/8" hose barb (ST Models: 1.5" Sanitary fitting to 14.3 mm hose barb)	¾" NPTF and NPTM to 5/8" hose barb	¾" NPTF and NPTM with 11 mm hose barb adapter	¾" NPTF and NPTM with 11 mm hose barb adapter	¾" NPTF and NPTM with 16 mm hose barb adapter	¾" NPTM with 11 mm hose barb adapter	¾" NPTM w/ ball valve stepped (7, 10.5, 13 mm) hose barb adapter ¾" NPTM with 11 mm hose barb adapter	¾" NPTM w/ ball valve stepped (7, 10.5, 13 mm) hose barb adapter ¾" NPTM with 11 mm hose barb adapter
Max Pressure Inlet (psi)	99	99	99	99	99	99	71	71	71
Max Pressure Diff. (psi)	<42	<42	<42	<42	<42	<42	<42	<42	<42
Filtration Area (cm 2)	45.3	113	530	45.3	113	530	12.5	43	113



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)