



Kit de Inspección Determinador de Concreto – CDIK

Código: CDIK

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The [concrete moisture test kit](#) for performing the [Tramex Complete Concrete Moisture Test System](#) for instant and precise testing of both Surface and In-Body concrete Moisture Content in floors and slabs using a unified gravimetric-based testing method.

The Tramex CMEX5 digital moisture meter allows for [non-destructive quantitative testing of concrete](#) and comparative testing per ASTM F2659.

The reusable Concrete Moisture Determinator Probe used with the CMEX5 allows for [in-depth moisture content probe testing](#) within the concrete, down to an extendable depth of up to 4" (100mm), Diameter 3/4" (19mm).

The CMEX5 also incorporates reusable plug-in Hygro-i2 ® RH probes for [in-situ testing of concrete as per ASTM F2170](#).

An infrared surface thermometer gives surface temperature and dew point conditions when used in conjunction with the CMEX5 hygrometer.

The Concrete Determinator Inspector Kit comes in a protective heavy-duty carrying case with die-cut foam lining. The [Tramex Meters App](#) allows you to [GeoTag test results](#), create, save and share reports and charts, as well as see your meter screen on your phone when using the CMEX5 extension handle.

Popular complementary product: [AP-F2170-B ASTM F2170 Accessory Pack](#) for RH testing; including reusable Hygro-i2 probes, hole liners, and tools.

1. [Concrete Moisture Encounter X5 - CMEX5](#).
2. [Free App](#) available for Android and iOS (phone not included).
3. [Concrete Moisture Determinator Probe](#).
4. [1 x Hygro-i2 ® Reusable Relative Humidity probe](#).
5. [Calibration Check Plate](#).
6. [Infrared Thermometer](#).
7. [Hole liners](#).
8. [Extension Handle](#).



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3



Imagen de galería 4



Imagen de galería 5




Imagen de galería 6

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)