



Contador y colocador de semillas por vacío

Código: B2-01-010568

Marca: Belltronic

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

It is used for seed placement, seed suction and seed placement during the seed germination experiment process.

Features

- 1. Used for seed counting, suction and placing in the course of seed germination.
- 2. Made up of main machine, suction tube and suction head.
- 3. With control button to control the suction power according to seed size.
- 4. With 5 different seed suction heads, its size and specification match with Petri dish, meet needs of different seed germination.

Especificaciones técnicas

Especificación	5 unidades
Temperatura	≤40°C
Potencia	1200W a 220V 50Hz
Alimentación eléctrica	AC220V,50Hz(Estándar); AC110V,60Hz(Opcional, transformador externo)
Placas de succión	5 unidades
Tamaño de succión	12*8.8(100 orificios, para maíz, 1 unidad); 16.7*12(1 unidad); 10.3*10.3(100 orificios, 2 unidades), Φ8(100 orificios/unidad)
Dimensiones del embalaje	600*350*260mm
Peso bruto	14kg

Aplicaciones

1. Check the working conditions

Check that the temperature of the area where you run germination tests stays within the instrument limit.

- **Temperature:** ≤40°C

2. Plan the installation

Confirm the available power supply and the power the instrument requires.

- **Power:** 1200W at 220V 50Hz



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

- **Power Supply:** AC220V,50Hz(Standard); AC110V,60Hz(Optional, external transformer)

Consider the space needed to receive the package.

- **Packing Size:** 600*350*260mm

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)