



Microscopio estéreo zoom ocular Distancia de trabajo 80 mm

Código: B2-01-010659

Marca: Belltronic

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Microscopio estereoscopico.

Especificaciones técnicas

Compara variantes usando especificaciones técnicas validadas.

Especificación	BM-12TC - Working distance 80mm - Magnification
Model	BM-12TC
Eyepiece	Working distance 80mm
High eye point, large field of view, flat field eyepiece	Magnification
6.3x	34.92mm
80x	2.75mm
Zoom ratio	12.5:1
Total magnification	6.3x-80x
Interpupillary distance	50-76mm
Nosepiece	2-port objective nosepiece for simultaneous mounting of 2 primary objectives
Body	Vertical arm type coarse and fine adjustment coaxial focusing mechanism, bracket lens body integrated, focusing stroke 50mm, fine adjustment accuracy 0.002mm
Light source	Intermediate magnification 1.5X; with 1/4 λ waveplates, 360-degree rotation; 20W LED cold light source generator with brightness adjustment knob; with flexible dual optical fibers, length 1m
Base	Ultra-thin base, multiple LEDs (total power 5W), base with color temperature display and brightness display (color temperature range: 3000-5600K)

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)