



Cabina limpia (cabina de flujo descendente) 1920-4880 mm utiles

Código: B2-01-010119

Marca: Belltronic

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Clean booth is a kind of air purifying equipment providing partial high clean environment, it's the easiest and fastest way to build a simple clean room. Equipped with a lot of clean level and space collocation, it can be designed as request. Main characteristics: simple use, good flexibility, easy installation, short construction time, and movable. It can be installed in part of clean room of general level which requires high cleanliness to save cost.

Características

1. Customized design is welcomed.
2. It can be used singly or combined.
3. Compared with civil type and fabricated type clean room of hundred clean level, it has low running cost and fast effect and can be easily installed.
4. Modular construction, easy to increase clean level, good expansion and reusable, convenient movement(Universal wheel can be installed).

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	1	2	3	4
Tamaño externo (A*P*Al)	2000*1500*2530mm	3000*2000*2530mm	4000*3000*2530mm	5000*5000*2530mm
Tamaño interno (A*P*Al)	1920*1380*2140mm	2920*1880*2115mm	3880*2880*2095mm	4880*4880*2095mm
Filtros HEPA	99.995% efficiency at 0.3µm	99.995% efficiency at 0.3µm	99.995% efficiency at 0.3µm	99.995% efficiency at 0.3µm
Consumo	800W	1500W	2800W	5500W
N.º de FFU	4pcs	6pcs	12pcs	25pcs
Nivel de limpieza	ISO 5(Class 100), Class A	ISO 5(Class 100), Class A	ISO 5(Class 100), Class A	ISO 5(Class 100), Class A
Sistema de control	Microprocessor control system	Microprocessor control system	Microprocessor control system	Microprocessor control system
Material del tubo rectangular	Aluminium alloy	Aluminium alloy	Aluminium alloy	Aluminium alloy
Material de pared	Anti-static dustproof curtain	Anti-static dustproof curtain	Anti-static dustproof curtain	Anti-static dustproof curtain
Ventilador	Built-in centrifugal blower, Speed adjustable	Built-in centrifugal blower, Speed adjustable	Built-in centrifugal blower, Speed adjustable	Built-in centrifugal blower, Speed adjustable
Lámpara UV (1)	40W*2	40W*2	40W*3	40W*5
Lámpara UV (2)	Emission of 253.7nanometers with UV timer	Emission of 253.7nanometers with UV timer	Emission of 253.7nanometers with UV timer	Emission of 253.7nanometers with UV timer

Especificación	1	2	3	4
Lámpara de iluminación (1)	16W*1	16W*2	16W*3	16W*5
Lámpara de iluminación (2)	LED lamp, Illumination: $\geq 300\text{lux}$	LED lamp, Illumination: $\geq 300\text{lux}$	LED lamp, Illumination: $\geq 300\text{lux}$	LED lamp, Illumination: $\geq 300\text{lux}$
Velocidad del aire	0.1~0.6m/s, average 0.45m/s	0.1~0.6m/s, average 0.45m/s	0.1~0.6m/s, average 0.45m/s	0.1~0.6m/s, average 0.45m/s
Ruido	$\leq 75\text{db}$	$\leq 75\text{db}$	$\leq 75\text{db}$	$\leq 75\text{db}$
Alimentación eléctrica	AC220V $\pm 10\%$, 50/60Hz; 110V $\pm 10\%$, 60Hz	AC220V $\pm 10\%$, 50/60Hz; 110V $\pm 10\%$, 60Hz	AC220V $\pm 10\%$, 50/60Hz; 110V $\pm 10\%$, 60Hz	AC220V $\pm 10\%$, 50/60Hz; 110V $\pm 10\%$, 60Hz
Peso bruto	390kg	670kg	1100kg	2900kg
Peso neto	355kg	625kg	1020kg	2800kg
Tamaño del embalaje (A*P*Al)	2110*930*920mm 2280*660*500mm	3080*980*1280mm 3080*660*550mm	3200*880*980mm*1 3200*1820*1350mm*1	4080*980*1280mm*3 1260*660*1280mm 5080*460*500mm
Diseño personalizado de nivel de limpieza, tamaño o material disponible	Customized design for clean level, size or material is available.	Customized design for clean level, size or material is available.	Customized design for clean level, size or material is available.	Customized design for clean level, size or material is available.

Aplicaciones

Disruptor celular ultrasonico: elija la variante comparando Tamaño interno (An. x Pr. x Al.), Tamaño externo (An. x Pr. x Al.) y Números de FFU.

Que cambia entre variantes

Configuración 1: Tamaño interno (An. x Pr. x Al.): 1920*1380*2140mm; Tamaño externo (An. x Pr. x Al.): 2000*1500*2530 mm; Números de FFU: 4 piezas.

Configuración 2: Tamaño interno (An. x Pr. x Al.): 2920*1880*2115mm; Tamaño externo (An. x Pr. x Al.): 3000*2000*2530 mm; Números de FFU: 6 piezas.

Configuración 3: Tamaño interno (An. x Pr. x Al.): 3880*2880*2095mm; Tamaño externo (An. x Pr. x Al.): 4000*3000*2530mm; Números de FFU: 12 piezas.

Configuración 4: Tamaño interno (An. x Pr. x Al.): 4880*4880*2095mm; Tamaño externo (An. x Pr. x Al.): 5000*5000*2530mm; Números de FFU: 25 piezas.

Escenarios de uso recomendados

Use esta configuración si necesita tamaño interno (an. x pr. x al.): 1920*1380*2140mm y tamaño externo (an. x pr. x al.): 2000*1500*2530 mm.

Use esta configuración si necesita tamaño interno (an. x pr. x al.): 2920*1880*2115mm y tamaño externo (an. x pr. x al.): 3000*2000*2530 mm.

Use esta configuración si necesita tamaño interno (an. x pr. x al.): 3880*2880*2095mm y tamaño externo (an. x pr. x al.): 4000*3000*2530mm.

Use esta configuración si necesita tamaño interno (an. x pr. x al.): 4880*4880*2095mm y tamaño externo (an. x pr. x al.): 5000*5000*2530mm.



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Cómo elegir rápido

Revise primero Tamaño interno (An. x Pr. x Al.), Tamaño externo (An. x Pr. x Al.) y Números de FFU; si esos puntos calzan con el proceso, confirme los accesorios y condiciones de instalacion.

Recomendación de compra

Seleccione la configuracion que cubra Tamaño interno (An. x Pr. x Al.), Tamaño externo (An. x Pr. x Al.) y Números de FFU.

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)