



## Dec Scanner - DS2

**Código:** DS2

**Marca:** Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

## Detalle

The Tramex Dec Scanner is a mobile non-destructive impedance scanner designed for the instant surveying of moisture conditions in flat roofing and waterproofing systems per ASTM D7954.

The Dec Scanner roof moisture meter detects and measures leaks within the roofing structure. Featuring three ranges of sensitivity and with a maximum depth penetration of 6" (152mm), the Dec Scanner enables the inspection of a variety of roof membranes and insulation thicknesses.

Readings are instant and a flat roof area of up to 100,000 square feet can be reasonably covered in a day.

As it is easy and safe to use with no regulatory restrictions or operating license required, the Dec Scanner is ideal for water leak detection and integrity testing in roofing materials.

- Complies to ASTM D7954
- Non-destructive impedance moisture meter.
- Three ranges of sensitivity enabling the inspection of a variety of roof membranes and insulation thicknesses.
- Ergonomic easy-reach and easy to operate control panel.
- Leak tracing, water leak detection, problem sourcing, and an instantaneous and clear indication of roof condition.
- Fast readings over large roof areas in a short time frame.
- Work in normal daylight hours.
- Faster and more user friendly than nuclear meters.
- Easy and safe to use with no regulatory restrictions or operating license required.
- Dependable solid state circuitry and rugged molded body for long-term reliability.
- Battery powered - 9 Volt PP3.
- Detect moisture in roofs without tearing them apart.



Importadora Gyb Limitada  
Padre orellana 1476  
Santiago CL13101 Chile

## Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1




Imagen de galería 2




Imagen de galería 3



Imagen de galería 4



Imagen de galería 5



Importadora Gyb Limitada  
Padre orellana 1476  
Santiago CL13101 Chile

**Siguiente paso:** [ver producto en Cotecno](#) | [solicitar cotización](#)