



Building Survey Master Kit - BSMK

Código: BSMK

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The Tramex Building Survey Master Kit is the ultimate kit for non-destructive testing of moisture content and humidity conditions in drywall, wood, plaster, brick, ceramic tiles, resilient flooring, laminates and roofing and numerous building materials and air spaces.

The RWS Roof & Wall Scanner allows for instant, non-destructive evaluation of moisture conditions deep within wall and roofing systems.

moisture meter measures moisture content in wood and drywall and provides comparative readings in a variety of building materials.

The MEX5 moisture meter features dual depth measuring range. Deep Depth penetration of up to 1¼" (30mm) and Shallow Depth penetration of up to ⅜" (9mm). The dual depth readings of surface and core moisture can be compared to eliminate the influence of the substrate when testing coverings.

It also features a built-in hygrometer for ambient conditions and psychrometric values, an Infrared Surface Thermometer and also incorporates the external RH probe for in-situ equilibrium RH readings, as well as the pin probe for wood, drywall, and WME readings. The insulated 200mm (7.8") pins and narrow 127mm (5") RH probe allow for deep wall cavity and insulation pin probing.

Bluetooth connectivity to the Tramex Meters App allows for visualization of readings, moisture mapping and data reporting to mobile devices, to GeoTag test results, create, save and share photos, reports and charts, as well as see your meter screen on your phone when extending to hard to reach places.

The Tramex Building Survey Master Kit comes with extension handles and a protective heavy-duty carrying case with die-cut foam lining.

1. RWS - Roof and Wall Scanner
2. Moisture Encounter MEX5
3. Heavy-duty pin-type electrode
4. 7.8" (200mm) insulated pins for in-depth penetration using pin probe
5. Short narrow Wand Relative Humidity Probe
6. Calibration Check Salts for Relative Humidity probe.
7. Extension Handle



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3



Imagen de galería 4



Imagen de galería 5



Imagen de galería 6

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)