



FLOORING MASTER KIT - FMK

Código: FMK

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The Tramex FMK is the ultimate kit for instant, non-destructive quantitative moisture testing of concrete and wood flooring, as well as RH and dew point testing of concrete and ambient conditions, both pre- & post-application of floor covering materials.

Featuring the Tramex CMEX5 digital concrete moisture meter for [non-destructive quantitative moisture testing of concrete](#) using Gravimetric testing as a baseline, comparative testing per ASTM F2659, and ambient conditions.

The CMEX5 incorporates bayonet plug-in heavy-duty pin-probes measuring moisture content in wood or WME in other building materials.

The CMEX5 also incorporates reusable Tramex Hygro-i2 RH probes for [in-situ testing of concrete as per ASTM F2170](#). Tramex Hygro-i2 RH probes can be used with the Tramex Feedback Datalogger to give live readings and time logs of relative humidity, temperature and dew point in situ and in the environment.

An infrared surface thermometer gives surface temperature and dew point conditions used in conjunction with the CMEX5 hygrometer.

The Tramex ME5 allows for moisture testing of wood and includes a shallow-depth feature to eliminate the effect of the substrate when needed.

The Tramex Flooring Master Kit comes with an extension handle in a heavy-duty Tramex travel case. Bluetooth connectivity to the [Tramex Meters App](#) allows for visualization of readings and data reporting to mobile devices, to [GeoTag test results](#), create, save and share photos, reports and charts, as well as see your meter screen on your phone when extending to hard to reach places.

1. [Concrete Moisture Encounter X5 - CMEX5](#).
2. [Moisture Encounter 5 - ME5](#).
3. [Free App available for Android and iOS \(phone not included\)](#).
4. [Feedback Datalogger - DL-RHTX](#).
5. [3 x Hygro-i2® Relative Humidity probes](#).
6. [Heavy-duty Pin-type Wood Probe](#).
7. [Hammer-action pin-type electrode](#).
8. [Infrared Thermometer](#).
9. [Calibration Check Salt](#).
10. [Hole liners](#).
11. [Extension Handle](#).



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3



Imagen de galería 4



Imagen de galería 5



Imagen de galería 6

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)