



WATER DAMAGE RESTORATION INSPECTOR KIT - WDIK

Código: WDIK

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The Tramex Water Damage Restoration Inspector Kit is the complete kit for moisture content and relative humidity testing and monitoring of ambient conditions, concrete, wood, tiles, drywall, plaster and numerous building materials after water damage.

Walls and floors

Featuring the Tramex [ME5](#) for dual-depth, non-invasive testing of moisture conditions in drywall, wood, plaster, brick, tiles, resilient flooring, laminates and roofing. The [ME5](#) has a dual-depth feature to allow for the elimination of substrate influence on readings.

Concrete

The Tramex [CMEX5](#) digital concrete moisture meter allows for quantitative moisture content measurement using Gravimetric testing as a baseline, comparative testing of concrete and ambient conditions measurement. The CMEX5 incorporates a bayonet plug-in port for the heavy-duty pin-probe to measure moisture content in wood or WME in other building materials as well as Relative Humidity readings with the reusable Tramex Hygro-i2 RH probe.

Ambient conditions

The Tramex [Feedback Datalogger](#) gives live readings and time logs relative humidity, temperature and dew point in the environment and in materials and air spaces with the plug-in relative humidity probe. An [infrared surface thermometer](#) gives surface temperature and dew point conditions used in conjunction with the CMEX5 hygrometer.

Moisture mapping

Bluetooth connectivity to the [Tramex Meters App](#) allows for visualization of readings, [moisture mapping](#) and data reporting to mobile devices, to [GeoTag test results](#), create, save and share photos, reports and charts, as well as see your meter screen on your phone when extending to hard to reach places.

The Tramex Water Damage Restoration Inspection Kit comes with an [extension handle](#) in a protective heavy-duty carrying case with die-cut foam lining.

1. [Concrete Moisture Encounter X5 - CMEX5](#).
2. [Moisture Encounter 5 - ME5](#).
3. [Feedback Datalogger - DL-RHTX](#).
4. [Free App available for Android and iOS](#) (phone not included).
5. [Heavy-duty pin-type wood probe](#).
6. [5" \(127mm\) short narrow Relative Humidity probe](#).
7. [7.8" \(200mm\) insulated pins for in-depth penetration](#).



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

8. [Calibration Check Salts.](#)
9. [Infrared Thermometer.](#)
10. [Extension Handle.](#)



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3



Imagen de galería 4



Imagen de galería 5



Imagen de galería 6

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)