



Moisture Encounter ME5

Código: ME5

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The Tramex Moisture Encounter ME5, the updated Moisture Encounter Plus, is a non-destructive moisture meter for detecting moisture in most building materials. As a [wood moisture meter](#), the Moisture Encounter ME5 provides actual moisture content % readings. The ME5 also functions as a moisture meter for [drywall](#), plaster, roofing, tile and masonry to help determine moisture content levels in walls, ceilings and [floors](#).

Dual Depth Moisture Meter

The Dual Depth feature of the ME5 makes it possible to determine where the moisture is located within the material. The shallow-depth readings, up to 3/8" (9mm), and deep-depth readings, up to 1 1/4" (30mm), can be used to compare surface moisture and core moisture and eliminate the influence of the substrate when testing coverings.

Measures Wood %MC

The ME5 is a pinless [moisture meter for wood](#) and is calibrated to read actual moisture content percentage (MC%) in wood without the need for pins damaging the surface. The wood scale shows a 5-30% moisture content range. Wood adjustment tables are available for specific wood type density adjustments where necessary.

Pre-calibrated for many building materials

The ME5 detects elevated moisture levels within the most common building materials and is pre-calibrated to the various densities of materials such as drywall, plaster, roofing, tile and masonry.

This general moisture reader detects moisture through paint, wallpaper, drywall, ceramic tiles, floor coverings, wood, ceiling tiles, roofing membranes, and asphalt composition shingles and makes it the best moisture meter for testing in, through and behind a wide range of building materials.

Moisture Mapping & Data Documentation

Moisture readings can be visualized with the [Tramex Meters App](#) and turned into [moisture maps](#), reports and charts for sharing. Bluetooth connectivity to mobile devices also helps to [GeoTag](#) test results, create, save and share photos.

Moisture Encounter Plus is now Moisture Encounter ME5

The ME5 moisture meter is the new and improved version of the well-established and trusted Moisture Encounter Plus - MEP - moisture meter, which has been a favourite amongst moisture professionals for many years.

Moisture Meter Features

- 5 Ranges of sensitivity: Wood & Timber / Shallow Depth / Drywall & Roofing / Plaster & Tile / Masonry
- Dual-Depth penetration allows for comparative of surface and core moisture and elimination of substrate influence on the testing of coverings.
- Deep signal penetration, up to 1¼" (30mm) in wood and drywall, detects elevated moisture through most covering materials without having to damage or puncture the materials being tested.
- Shallow Depth scale is designed to have a field penetration of up to ⅜" (9mm).
- Wide range of readings from 5% to 30% on Wood Scale and 0 to 100 on comparative scale for all other materials.
- Detects moisture through paint, wallpaper, drywall, ceramic tiles, floor coverings, wood, ceiling tiles, roofing membranes, and asphalt composition shingles.
- Bluetooth connection to accompanying IOS & Android App allowing for continual development and integration of apps and reporting.
- Hold Function which enables the user to "freeze" the reading, useful when taking readings where the meter face may not be visible.
- High Moisture Audio Warning Tone which can be enabled or disabled.
- Large clear easy to read analog display giving meaningful readings.
- Rugged ergonomically designed enclosure.



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3




Imagen de galería 4



Imagen de galería 5

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)