



Roof and Wall Moisture Scanner - RWS

Código: RWS

Marca: Tramex

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#) | [Galería de imágenes](#)

Detalle

The Tramex Roof and Wall Scanner is an instant, precise, multi-mode, non-destructive impedance scanner for evaluating moisture conditions in roofing (as per ASTM D7954), EIFS, foam insulation systems & other building envelope applications.

The RWS Multi-mode function allows for depth penetration and sensitivity selection and can help trace leaks and pin-point their source, which makes it a very beneficial moisture detector for walls and roofs.

- Complies with ASTM D7954.
- For non-destructive moisture evaluation of roofs, EIFS, foam insulation systems & other building envelope applications.
- To evaluate the extent of the moisture problem and help trace and pin-point its source.
- Multi-mode functions allowing for depth penetration and sensitivity selection.
- Fast and easy to operate giving instant clear readings.
- "Hold" function facilitates ease of recording readings.
- Lightweight, handheld and battery operated.
- Telescopic handle (for use on roofs).
- Inexpensive to purchase and operate compared to other non-destructive testing methods.
- Professional roofing moisture meter for the water damage industry



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Galería de imágenes

Mostrando hasta 6 imágenes de la galería.



Imagen de galería 1



Imagen de galería 2



Imagen de galería 3




Imagen de galería 4

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)