



Bano de agua - 13 litros - Termostatico (220/110 V; 50/60 Hz)

Código: B-01-0101309

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

The water bath is mainly used in the laboratories and laboratories of colleges and universities, scientific research enterprises and institutions. Distillation, drying, concentration and temperature staining of various chemical samples of biological products, examination of serum and biochemical experiments, constant temperature culture and boiling disinfection of syringes and small surgical instruments.

Características

1. The shell adopts cold plate spraying, which improves the anti-corrosion ability of the whole machine.
2. The water tank is made of 304 stainless steel, which is resistant to high temperature, corrosion and rust.
3. Adjustable ring cover to meet the needs of different sizes of experimental instruments.
4. Real-time temperature value display, accurate temperature control, countdown display.
5. Hidden stretch drain, beautiful, convenient and durable.

Especificaciones técnicas

SKU	B-01-0101309
Capacidad	13 litros
Rango de temperatura	Temperatura ambiente +5~99,9 °C
Precisión de temperatura	0,1 °C
Fluctuación de temperatura	±0,5 °C
Uniformidad de temperatura	±0,5 °C
Rango de tiempo	1~999 min
Pantalla	LED
Protección anti-sequedad	Sí
Consumo	800 W
Fuente de alimentación	CA 220 V, 50/60 Hz (estándar); 110 V, 50/60 Hz (opcional)
Tamaño interno (L*An.*Al.)	305*305*140 mm
Tamaño externo (L*An.*Al.)	365*365*195 mm
Peso neto	4,3 kg
Tamaño del embalaje (L*An.*Al.)	395*395*240 mm
Peso bruto	5,3 kg
Núm. máx. φ13 mm x 40	3
Núm. máx. φ14 mm x 40	3

Núm. máx. $\varnothing$ 16 mm x 40	3
Núm. máx. $\varnothing$ 17 mm x 40	2
Núm. máx. $\varnothing$ 19 mm x 40	2
Núm. máx. $\varnothing$ 21 mm x 40	2
Núm. máx. $\varnothing$ 23 mm x 40	2
Núm. máx. $\varnothing$ 25 mm x 40	/
Núm. máx. $\varnothing$ 27 mm x 40	/
Núm. máx. $\varnothing$ 30 mm x 40	/
Núm. máx. $\varnothing$ 17 mm x 12	8
Núm. máx. $\varnothing$ 19 mm x 12	5
Núm. máx. $\varnothing$ 21 mm x 12	4
Núm. máx. $\varnothing$ 23 mm x 12	4
Núm. máx. $\varnothing$ 27 mm x 12	3
Núm. máx. $\varnothing$ 30 mm x 12	3
Núm. máx. $\varnothing$ 32 mm x 12	3

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)