



SCB ASTM D8044

Description	Qty	Part #
Load frame	1	HM-5125A.3F
Load Cell, Pancake 11,000 lbf (50kN)	1	HM-2300.100CP
Linear Potentiometer 1" (25mm)	1	HM-2305.10
Potentiometer Bracket	1	HM-5000BR
SCB head, 150mm	1	H-1351



SCB (I-Fit Method) AASHTO T393

Description	Qty	Part #
Load frame	1	HM-5125A.3F
Load Cell, Pancake 11,000 lbf (50kN)	1	HM-2300.100CP
Linear Potentiometer 1" (25mm)	1	HM-2305.10
Potentiometer Bracket	1	HM-5000BR
SCB head, 150mm	1	H-1351



TSR AASHTO T283

Description	Qty	Part #
Load frame	1	HM-5125A.3F
Load Cell, Pancake 11,000 lbf (50kN)	1	HM-2300.100CP
Lottman head, 6" (150mm)	1	H-1369 H-1369M
Lottman head, 4" (100mm)	1	H-1349 H-1349M



Marshall ASTM D6927, AASHTO T245

Description	Qty	Part #
Load frame	1	HM-5125A.3F
Load Cell, Pancake 11,000 lbf (50kN)	1	HM-2300.100CP
Linear Potentiometer 1" (25mm)	1	HM-2305.10
Potentiometer Bracket	1	HM-5000BR
Marshall Breaking Head, 6" (150mm)	1	H-1362
Marshall Breaking Head, 4" (100mm)	1	H-1342 H-1342M



Scan Me!
For more information.