

**Trowel, Plasterer-Type**

Plasterer-type trowel's flat rectangular blade is fastened to the mounting and wood handle with stainless steel pins. Dimensions: 4.5" x 10" (114 x 254mm).

Trowel, Plasterer-Type **H-3762**
 Ship wt. 1lbs. (0.45kg)

Trowel, Forged Steel

Forged steel trowel for mixing cement batches, filling molds, etc., has flat-pointed blade and rubber/plastic handle. Dimensions: 2.75" x 5" (70 x 127mm).

Trowel, 2.75" x 5" (70 x 127mm) **H-3760**
Trowel, 5.25" x 10" (133 x 254mm) **H-3780**
 Ship wt. 0.4lbs. (0.2kg)

Trowel, ASTM

ASTM C109; AASHTO T106

Forged steel trowel for striking off molds, etc., has edges ground straight and rubber/plastic handle. Dimensions: 2.75" x 5" (70 x 127mm).

Trowel, ASTM **H-3761**
 Ship wt. 0.4lbs. (0.2kg)

Spoon

For mixing and transferring soils, handling corrosive chemicals, etc., stainless steel spoon is 13" (330mm) long.

Spoon **H-4974**
 Ship wt. 0.5lbs. (0.2kg)

Preparation Knife

Used for sample preparation and general lab work, knife has 6" long thin, sharp blade and wood handle.)

Preparation Knife **H-4973**
 Ship wt. 0.5lbs. (0.2kg)

Spatulas, Straight Edge

ASTM C185, C780; AASHTO T137 (H-4907 only)

Flexible stainless steel blades with straight edges and rounded ends. Blade is riveted into wooden handle. H-4907 complies with ASTM C185, C780; AASHTO T137.

Spatula, 4" x .75" (102mm x 19mm) **H-4904**
Spatula, 6" x 1" (152mm x 25mm) **H-4906**
Spatula, 6" x .5" (152mm x 13mm), ASTM **H-4907**
Spatula, 8" x 1.25" (204mm x 32mm) **H-4908**
Spatula, 10" x 1.25" (254mm x 32mm) **H-4910**
 Ship wt. 0.5lbs. (0.2kg)

Step-Up and Down Transformers

Step-Up and down transformers allow the user to use 115-volt electrical equipment on a 230-volt line current, and allow 230-volt equipment to be used on 115V line current. Features case and core internally connected to third conductor of NEMA-standard cord and receptacle for safety. Has 3-conductor, 8" (2.4m) line cord and plug on primary side and female receptacle as output connection.

Power	Ship Wt.	Model
300-watt.	10 lbs. (4.5kg)	H-1042A
500-watt.	12 lbs. (5.4kg)	H-1042A.5
750-watt.	16 lbs. (7.3kg)	H-1042A.7
1,000-watt.	17 lbs. (7.7kg)	H-1042A.10
1,500-watt.	21 lbs. (9.5kg)	H-1042A.15
1,750-watt.	21 lbs. (9.5kg)	H-1042A.17
2,000-watt.	28 lbs. (12.7kg)	H-1042A.20
2,500-watt.	28 lbs. (12.7kg)	H-1042A.25
3,000-watt.	28 lbs. (12.7kg)	H-1042A.30

Step-Up and Down Transformers See table above

see table