



H-1336AD



H-1346D



H-1356D

4" Automatic, Single Compactor (64 Blows per min.) with Stationary Base

ASTM D6926, AASHTO T245, PTM705, R68

This compactor automatically compacts samples at a preset number of 64 hammer blows a minute and shuts off at completion. The compactor features a stationary base with flat-foot hammer. Unit includes mechanical compactor, automatic counter, ASTM-compliant oak compaction pedestal, (1) hammer and (1) H-1341A mold assembly. Additional mold and hammer assemblies are recommended for efficient testing operations, allowing you to preheat multiple molds and hammers to speed testing.

- 4" Single Compactor, 115V 60Hz H-1336AD
- 4" Single Compactor, 230V 60Hz H-1336AD.2F
- 4" Single Compactor, 230V 50Hz H-1336AD.5F

Ship wt. 226lbs. (102.5kg)

4" Automatic, Single Compactor (55 Blows per min.) with Stationary Base

ASTM D6926, AASHTO T245, PTM705, R68

This compactor automatically compacts samples at a preset number of 55 hammer blows a minute and shuts off at completion. The compactor features a stationary base with flat-foot hammer. Unit includes mechanical compactor, automatic counter, ASTM-compliant oak compaction pedestal, (1) hammer and (1) H-1341A mold assembly. Additional mold and hammer assemblies are recommended for efficient testing operations, allowing you to preheat multiple molds and hammers to speed testing.

- 4" Single Compactor, 115V 60Hz H-1336BD
- 4" Single Compactor, 230V 60Hz H-1336BD.2F
- 4" Single Compactor, 230V 50Hz H-1336BD.5F

Ship wt. 226lbs. (102.5kg)

4" Automatic, Double Compactor with Rotating Base

ASTM D6926, AASHTO T245, PTM705

This compactor automatically compacts two samples simultaneously at a preset number of hammer blows and shuts off at completion. The compactor features rotating bases with tapered-foot hammers. Unit includes mechanical compactor, automatic counter, ASTM-compliant oak compaction pedestal, (2) hammers and (2) H-1337 mold assemblies. Additional mold and hammer assemblies are recommended for efficient testing operations, allowing you to preheat multiple molds and hammers to speed testing.

- 4" Double Compactor, 115V 60Hz H-1346D
- 4" Double Compactor, 230V 60Hz H-1346D.2F
- 4" Double Compactor, 230V 50Hz H-1346D.5F

Ship wt. 265lbs. (120.2kg)

4" Automatic, Triple Compactor with Rotating Base

ASTM D6926, AASHTO T245, PTM705

This compactor automatically compacts three samples simultaneously at a preset number of hammer blows and shuts off at completion. The compactor features rotating bases with tapered-foot hammers. Unit includes mechanical compactor, automatic counter, ASTM-compliant oak compaction pedestal, (3) hammers and (3) H-1337 mold assemblies. Additional mold and hammer assemblies are recommended for efficient testing operations, allowing you to heat multiple molds and hammers to speed testing.

- 4" Triple Compactor, 115V 60Hz H-1356D
- 4" Triple Compactor, 230V 60Hz H-1356D.2F
- 4" Triple Compactor, 230V 50Hz H-1356D.5F

Ship wt. 351lbs. (181.4kg)

Replacement Parts for Standard-Duty, Automatic Compactors

Item	Model #
4" hammer with flat foot (stationary base) for H-1336D	H-1338A
4" hammer with tapered foot (rotating base) for H-1346D, H-1356D	H-1338B
4" hammer with "Canadian" tapered foot (rotating base) for H-1346D, H-1356D	H-1338C
Marshall Compaction Mold 4" for Stationary Base Compactors	H-1341A
Marshall Compaction Mold 4" for Rotating Base Compactors	H-1337
Lift Chain for H-1336D, H-1346D and H-1356D	H-1336.21
Replacement Counter and proximity switch for Compactors, 115V	H-1334B
Replacement Counter and proximity switch for Compactors, 230V	H-1334B.4F
Replacement Pedestal for H-1336D Marshall Compactor	H-1347M
Replacement Pedestal for H-1346D Marshall Compactor	H-1347.2M
Replacement Pedestal for H-1356D Marshall Compactor	H-1347.3M