




### Augers, Bucket-Type, Quick-Connect

Quick-connect, button-and-hex coupling system allows components to connect and disconnect faster and with less hassle than threaded systems. Quick-connect connections, are not compatible with slide hammers. Bucket augers offer outstanding durability and allow access to deeper depths. The regular auger bit is designed for ordinary soil sampling. The sand auger bit is used for dry, sandy soils. Mud auger bits are designed for sampling heavy, wet soil or clay samples; opening facilitates removal of wet samples. Heat treated, high carbon steel bits with tungsten carbide hard-surfaced edges. Bits are welded to a stainless steel cylinder.

| Augers, Bucket-Type, Quick-Connect |          |          |          |
|------------------------------------|----------|----------|----------|
| Size                               | Regular  | Sand     | Mud      |
| 2"                                 | H-4410QC | H-4430QC | H-4420QC |
| 2.25"                              | H-4411QC | H-4431QC | H-4421QC |
| 2.75"                              | H-4412QC | H-4432QC | H-4422QC |
| 3.25"                              | H-4413QC | H-4433QC | H-4423QC |
| 4"                                 | H-4414QC | H-4434QC | H-4424QC |

Augers, Bucket-Type, Quick-Connect See Chart

Ship wt. 3lb (1.37kg)

### Augers, Extensions, Quick-Connect

Extensions for use with the Augers above.

| Auger Extensions, Quick-Connect |          |
|---------------------------------|----------|
| Description                     | Model    |
| 2 ft. (610mm), Extension        | H-4442QC |
| 3 ft. (914mm), Extension        | H-4443QC |
| 4 ft. (1219mm), Extension       | H-4444QC |
| 5 ft. (1524mm), Extension       | H-4445QC |

Auger Extensions, Quick-Connect See Chart

Ship wt. 3lb (1.3kg)

### Augers, Bucket-Type, Threaded

Threaded connections use standard, national course, threads. 5/8" connections are the most common and least expensive. Augers, core samplers, probes, slide hammers, hammer-head handles, and kits are available with threaded connections. Bucket augers offer outstanding durability and allow access to deeper depths. The regular auger bit is designed for ordinary soil sampling. The sand auger bit is used for dry, sandy soils. Mud auger bits are designed for sampling heavy, wet soil or clay samples; opening facilitates removal of wet samples. Heat treated, high carbon steel bits with tungsten carbide hard-surfaced edges. Bits are welded to a stainless steel cylinder.

| Augers, Bucket-Type, Threaded |          |          |          |
|-------------------------------|----------|----------|----------|
| Size                          | Regular  | Sand     | Mud      |
| 2"                            | H-4410TH | H-4430TH | H-4420TH |
| 2.25"                         | H-4411TH | H-4431TH | H-4421TH |
| 2.75"                         | H-4412TH | H-4432TH | H-4422TH |
| 3.25"                         | H-4413TH | H-4433TH | H-4423TH |
| 4"                            | H-4414TH | H-4434TH | H-4424TH |

Augers, Bucket-Type, Threaded See Chart

Ship wt. 3lb (1.3kg)

### Augers, Extensions, Threaded

Extensions for use with the Augers above.

| Auger Extensions, Threaded |          |
|----------------------------|----------|
| Description                | Model    |
| 2 ft. (610mm), Extension   | H-4442TH |
| 3 ft. (914mm), Extension   | H-4443TH |
| 4 ft. (1219mm), Extension  | H-4444TH |
| 5 ft. (1524mm), Extension  | H-4445TH |

Auger Extensions, Threaded See Chart

Ship wt. 3lb (1.3kg)



### Auger Handles, Quick-Connect

Cross handles with quick-connect, button-and-hex coupling system connect and disconnect faster and with less hassle than threaded systems.

Auger, Cross-Handle, Padded H-4447QC

Auger, Cross-Handle, 16" Ratcheting H-4449QC

Ship wt. 2.6lb (1.3kg)

### Auger Handles, Threaded

Cross handles with threaded connections use standard, national course, threads. 5/8" connections and are the most common and least expensive handle attachment method.

Auger, Cross-Handle, Padded H-4447TH

Auger, Cross-Handle, 16" Ratcheting H-4449TH

Ship wt. 3lb (1.3kg)