



Portafiltros para membrana cerámica

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Holdes for Ceramic Membrane

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	47 mm · CELLULEDIS47E	47 mm · CELLULEDIS47S	47 mm · CELLULEDIS47V	90 mm · CELLULEDIS90ET	90 mm · CELLULEDIS90ST	90 mm · CELLULEDIS90VT	90 mm · CELLULEDIS90EF	90 mm · CELLULEDIS90SF	90 mm · CELLULEDIS90VF
Tipo de material	EPDM Version	Silicone Version	Viton Version	(Crossflow) / EPDM Version	(Crossflow) / Silicon Version	(Crossflow) / Viton Version	EPDM Version	Silicone Version	Viton Version
Diametro (mm)	47	47	47	90	90	90	90	90	90
Soporte	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel
Juntas toricas	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone
Conexion de entrada	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter
Conexion de salida	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter
Presion	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)
Tamano de filtro	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm
Area de filtracion	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²	13.1 cm ² / 56.3 cm ²
Temperatura de operacion	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)
Autoclave	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)