



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile



Nanofiltración de disolventes orgánicos

Código: N/D
Marca: STERLITECH
[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Nanofiltración con disolventes orgánicos

Nanofiltración con disolventes orgánicos (OSN)

Destilación por membrana

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	pack 1 - 1122177	pac k 1 - 112 217 8	pac k 1 - 112 217 9	pac k 1 - 112 075 1	pac k 1 - 112 075 2	pac k 1 - 112 075 3	pac k 5 - 112 218 0	pac k 5 - 112 218 1	pac k 5 - 112 218 2	pac k 5 - 112 221 4	pac k 5 - 112 221 5	pac k 5 - 112 221 6	pac k 5 - 112 219 6	pac k 5 - 112 219 7	pac k 5 - 112 219 8	pac k 5 - 112 220 2	pac k 5 - 112 220 3	pac k 5 - 112 220 4	pac k 5 - 112 078 2	pac k 5 - 112 078 3	pac k 5 - 112 078 4	pac k 5 - 112 078 5	pac k 5 - 112 078 6	pac k 5 - 112 078 8	pac k 5 - 112 078 9	pac k 5 - 112 079 0	pac k 5 - 112 079 1	pac k 5 - 112 079 2	pac k 5 - 112 079 3
Designacion	Nano-Filtration	Nan-o-Filtratio n	Nan-o-Filtratio n	Pura me m Sele ctiv e	Pura me m Perf orm anc e	Pura me m Flux	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Nan-o-Filtratio n	Pura me m Sele ctiv e	Pura me m Sele ctiv e	Pura me m Sele ctiv e	Pura me m Sele ctiv e	Pura me m Perf orm anc e	Pura me m Perf orm anc e	Pura me m Perf orm anc e	Pura me m Flux	Pura me m Flux	Pura me m Flux	Pura me m Flux
Polimero	Silicone polymer-based	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one poly mer - bas ed	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN	Silic one-coat ed PAN
Tamano	210 x 291mm	210 x 291 mm	210 x 291 mm	210 X 297 mm	210 X 297 mm	210 X 297 mm	47m m	47m m	47m m	CF0 16	CF0 16	CF0 16	CF0 42	CF0 42	CF0 42	Sep a	Sep a	Sep a	Sep a	CF0 42	CF0 16	47m m	Sep a	CF0 16	47m m	Sep a	CF0 42	CF0 16	47m m
Tamano de paquete	1	1	1	1	1	1	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
Rejilla	Flat_Sheet_Membranes	Flat Sh eet_Me mbrane s	Flat Sh eet_Me mbrane s	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)