



Sistemas de membrana montados en skid

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Sistemas de membrana montados en skid

Familia de sistemas de filtración tangencial montados en skid con configuraciones Hybrid, Pilot y Production; control digital, analógico o automatizado.

Selección de equipos previamente usados y reacondicionados disponible para compra o arriendo. Solicita información o revisa la ficha del paquete de arriendo de sistemas.

Especificaciones técnicas

Especificación	1190053	1190054	1190055	1190058	1190060	1190062	1190108	1190110	1190120
Tipo	Skid Hybrid digital 110 V	Skid Hybrid digital 230 V	Skid Hybrid analógico 110 V	Skid Pilot digital 230 V	Skid Pilot analógico 230 V	Skid Pilot analógico antiexplosión 230 V	Skid Pilot automatizado 230 V	Skid Hybrid automatizado 110 V	Skid Production analógico 460 V
Control	Digital	Digital	Analog	Digital	Analog	Analog XP	Automated solenoid	Automated solenoid	Analog
Líneas de proceso	2 Parallel Lines	2 Parallel Lines	2 Parallel Lines	2 Parallel Lines	2 Parallel Lines	2 Parallel Lines	2 Parallel Lines, solenoid	2 Parallel Lines, solenoid	2 Lines, Series or Parallel
Caudal	11.7 LPM (3.1 GPM)	11.7 LPM (3.1 GPM) @ 600 PSI y 6.7 LPM (1.8 GPM) @ 1000 PSI	11.7 LPM (3.1 GPM)	33.3 LPM (8.8 GPM)	33.3 LPM (8.8 GPM)	33.3 LPM (8.8 GPM)	33.3 LPM (8.8 GPM)	11.7 LPM (3.1 GPM)	129 LPM (34 GPM)
Presión máxima	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)	69 bar (1000 PSI)
Temperatura máxima	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)	82 C (180 F)
Alimentación eléctrica	110 V / 50-60 Hz / 1 Ph	230 V / 50-60 Hz / 1 Ph	110 V / 50-60 Hz / 1 Ph	230 V / 50-60 Hz / 3 Ph	230 V / 50-60 Hz / 3 Ph	230 V / 50-60 Hz / 3 Ph	230 V / 50-60 Hz / 3 Ph	110/230 V / 50-60 Hz / 1 Ph	460 V / 50-60 Hz / 3 Ph
Carcasa	1812 + Sepa CF 316SS	1812 + Sepa CF 316SS	1812 + Sepa CF 316SS	1812 + 2540 316SS	1812 + 2540 316SS	1812 + 2540 316SS	1812 + 2540 316SS	1812 + Sepa CF 316SS	2x 4040
Membrana	1812 0.5 m ² / Sepa 140 cm ²	1812 0.5 m ² / Sepa 140 cm ²	1812 0.5 m ² / Sepa 140 cm ²	1812 0.5 m ² / 2540 3.5 m ²	1812 0.5 m ² / 2540 3.5 m ²	1812 0.5 m ² / 2540 3.5 m ²	1812 0.5 m ² / 2540 3.5 m ²	1812 0.5 m ² / Sepa 140 cm ²	4040; serie 15+ m ²

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)