

Membrana de policarbonato teñido, membrana de policarbonato

Código: N/D
Marca: STERLITECH
[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Membrana de policarbonato teñida, membrana de policarbonato

Sterlitech ofrece dos versiones de filtros de membrana de PCTE pigmentados para cubrir la gama más amplia posible de aplicaciones: gris y negro.

La variante gris Es ideal para aplicaciones donde se pueden realizar tanto microscopía de fluorescencia como microscopía óptica convencional en la misma muestra, mientras que el negro es ideal para aplicaciones que requieren un contraste maximizado para estudios de microscopía óptica de partículas u organismos de colores claros.

¿Cuál es la diferencia entre los filtros de membrana hidrófilos e hidrófobos?

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	0.2 µm · 25 mm · pack 100 · 1270190	0.2 µm · 25 mm · pack 100 · 1270059	0.2 µm · 47 mm · pack 100 · 1270191	0.2 µm · 47 mm · pack 100 · 1270060	0.4 µm · 25 mm · pack 100 · 1270079	0.4 µm · 25 mm · pack 100 · 1270189	0.4 µm · 47 mm · pack 100 · 1270188	0.4 µm · 47 mm · pack 100 · 1270061	0.8 µm · 25 mm · pack 100	0.8 µm · 47 mm · pack 100	1 µm · 25 mm · pack 100	1 µm · 47 mm · pack 100	5 µm · 25 mm · pack 100	5 µm · 47 mm · pack 100	8 µm · 25 mm · pack 100	8 µm · 47 mm · pack 100
Tamaño de poro	0.2	0.2	0.2	0.2	0.4	0.4	0.4	0.4	0.8	0.8	1	1	5	5	8	8
Color de membrana	Gray	Black	Gray	Black	Black	Gray	Gray	Black	Black	Black	Black	Black	Black	Black	Black	Black
Diametro (mm)	25	25	47	47	25	25	47	47	25	47	25	47	25	47	25	47
Tamaño de paquete	100	100	100	100	100	100	100	100	100	100	100	100	100	100	100	100
Ensayo USP clase VI	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed	Passed
Union proteica BSA	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²	~5 µg/cm ²
Esterilizacion	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO	Gamma Irradiation, ETO
Temperatura maxima de operacion	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)	140 °C (284 °F)
Compatibilidad de sellado	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding	Ultrasonic, Heat, Radio Frequency, and Insert Molding
Rango de pH	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8	4-8
resistencia a explosion	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)	0.7 bar (10 psi)

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)