



Filtros cápsula de fibra de vidrio

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Filtros de cápsula de fibra de vidrio

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	1 µm · 9 cm (3.5 in) mm · 1470147	1 µm · 9 cm (3.5 in) mm · 1470148	1 µm · 9 cm (3.5 in) mm · 1470560	3 µm · 9 cm (3.5 in) mm
Tamano de poro	1	1	1	3
Area de filtracion (sqft)	3.7	3.7	4.95	0.5
Largo (in)	11.5	12.7	10	3.5
Membrana	Glass Microfiber (acrylic resin-bonded)	Glass Microfiber (acrylic resin-bonded)	Glass Microfiber (acrylic resin-bonded)	Glass Microfiber (acrylic resin-bonded)
Soporte de membrana	Polypropylene Microfiber	Polypropylene Microfiber	Polypropylene Microfiber	Polypropylene Microfiber
Carcasa	Polypropylene	Polypropylene	Polypropylene	Polypropylene
Jaula, nucleo y tapas	Polypropylene	Polypropylene	Polypropylene	Polypropylene
Conexiones	Hose barb, sanitary flange, or MNPT end-fittings	Hose barb, sanitary flange, or MNPT end-fittings	Hose barb, sanitary flange, or MNPT end-fittings	Hose barb, sanitary flange, or MNPT end-fittings
Diametro	9 cm (3.5 in)	9 cm (3.5 in)	9 cm (3.5 in)	9 cm (3.5 in)
Presion	5.5 bar (80 psi) @ 21°C (70°F) in Liquid, 3.8 bar (55 psi) @ 21°C (70°F)	5.5 bar (80 psi) @ 21°C (70°F) in Liquid, 3.8 bar (55 psi) @ 21°C (70°F)	5.5 bar (80 psi) @ 21°C (70°F) in Liquid, 3.8 bar (55 psi) @ 21°C (70°F)	5.5 bar (80 psi) @ 21°C (70°F) in Liquid, 3.8 bar (55 psi) @ 21°C (70°F)
Temperatura maxima de operacion	43°C (110°F) at 2.1 bar (30 psi)	43°C (110°F) at 2.1 bar (30 psi)	43°C (110°F) at 2.1 bar (30 psi)	43°C (110°F) at 2.1 bar (30 psi)
Autoclave	Up to 5 Cycles. 30 minutes @ 121°C	Up to 5 Cycles. 30 minutes @ 121°C	Up to 5 Cycles. 30 minutes @ 121°C	Up to 5 Cycles. 30 minutes @ 121°C

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)