




Filtros de membrana de poliéster hidrófobo (PETE)

Código: N/D
Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Filtros de membrana de poliéster hidrófobo (PETE)

Estos filtros de membrana de poliéster con grabado de huellas han sido tratados mediante un proceso patentado para hacerlos permanentemente hidrófobos y oleofóbicos. Presentan una estabilidad dimensional superior a la de los filtros de membrana de PTFE y una mejor resistencia térmica que los filtros de membrana de poliolefina. Además, estos filtros de PETE suelen tener una mayor presión de entrada de agua que los filtros de ventilación tradicionales con un tamaño de poro similar. A diferencia del PTFE y el polipropileno, el poliéster es compatible con la esterilización por radiación gamma y se puede soldar térmicamente a una amplia variedad de sustratos.

Proporcionamos los filtros y el soporte técnico para ayudarle a convertir su producto innovador de una idea a un prototipo y a escala comercial.

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	0.2 µm · 13 mm · pack 100	0.2 µm · 200 x 250 · pack 30	0.2 µm · 200 x 250 · pack 5	0.2 µm · 25 mm · pack 100	0.2 µm · 47 mm · pack 100	0.2 µm · 90 mm · pack 30	0.45 µm · 210 x 300 · pack 30	1.2 µm · 13 mm · pack 100	1.2 µm · 200 x 250 · pack 30	1.2 µm · 25 mm · pack 100	1.2 µm · 47 mm · pack 100
Tamaño de poro	0.2	0.2	0.2	0.2	0.2	0.2	0.45	1.2	1.2	1.2	1.2
Tamaño de paquete	100	30	5	100	100	30	30	100	30	100	100
Tamaño de hoja	—	200 x 250	200 x 250	—	—	—	210 x 300	—	200 x 250	—	—
Diámetro (mm)	13	—	—	25	47	90	—	13	—	25	47
tamaño (mm)	—	—	—	—	—	—	210 x 300	—	—	—	—
Material	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic	Nonwoven Support	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic	Polyester Hydrophobic
Espesor	36	36	36	36	36	36	5-9 mil	140	140	140	140
Soporte	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported	PET or unsupported
temperatura Resistance	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C	160â°C



Importadora Gyb Limitada
Padre orellana 1476
Santiago CL13101 Chile

Especificación	0.2 µm · 13 mm · pack 100	0.2 µm · 200 x 250 · pack 30	0.2 µm · 200 x 250 · pack 5	0.2 µm · 25 mm · pack 100	0.2 µm · 47 mm · pack 100	0.2 µm · 90 mm · pack 30	0.45 µm · 210 x 300 · pack 30	1.2 µm · 13 mm · pack 100	1.2 µm · 200 x 250 · pack 30	1.2 µm · 25 mm · pack 100	1.2 µm · 47 mm · pack 100
Chemical compatibilidad	Very good for Medical, Life Science, and Automotive	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve	Very good for Medical, Life Science, and Automoti ve
Esterilizacion	Autoclavable, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam	Autoclav able, EtO, Gamma, E-Beam

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)