




PTFE Unlaminated Membrane Filters

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

PTFE Unlaminated Filtros de membrana

These PTFE filters are chemically and biologically inert, stable up to 260°C, and will withstand the majority of concentrated acids and bases and are especially useful for environments that contain water vapor. They are manufactured through a patented process where the membranes are stretched biaxially to form a high-porosity, uniformly thick, thermostable, pure ePTFE structure.

We provide the filters and technical support to help you take your breakthrough product from an idea to a prototype, to commercial scale.

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	0.2 μm · 13 mm · pack 50	0.2 μm · 14.2 mm · pack 10	0.2 μm · 22.5 mm · pack 50	0.2 μm · 29.3 mm · pack 10	0.2 μm · 30.0 mm · pack 1	0.2 μm · 47 mm · pack 50	0.2 μm · 90 mm · pack 10	0.45 μm · 13 mm · pack 50	0.45 μm · 25 mm · pack 5	0.45 μm · 29.3 mm · pack 10	0.45 μm · 30.0 mm · pack 1	0.45 μm · 47 mm · pack 50	0.45 μm · 90 mm · pack 10	1 μm · 13 mm · pack 50	1 μm · 25 mm · pack 50	1 μm · 25.4 mm · pack 1	1 μm · 47 mm · pack 50	1 μm · 63.5 mm · pack 100	1 μm · 90 mm · pack 100	1 μm · 90 mm · pack 10	10 μm · 13 mm · pack 50	10 μm · 25 mm · pack 50	10 μm · 25 mm · pack 5	10 μm · 30.0 mm · pack 1	10 μm · 47 mm · pack 10	10 μm · 90 mm · pack 10	3 μm · 47 mm · pack 100	5 μm · 13 mm · pack 50	5 μm · 25 mm · pack 5	5 μm · 25 mm · pack 50	5 μm · 47 mm · pack 50	5 μm · 90 mm · pack 10
Tamano de poro	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.45	0.45	0.45	0.45	0.45	0.45	1	1	1	1	1	1	1	10	10	10	10	10	10	3	5	5	5	5	5
Tamano de paquete	50	10	50	10	50	10	50	50	50	10	1	50	10	50	50	1	50	100	100	10	50	50	50	50	50	100	50	50	50	50	50	10
Diámetro (mm)	13	14.2	25	29.3	—	47	90	13	—	25	—	47	90	13	—	—	47	63.5	9.53	90	13	—	25	330X3000	47	90	47	13	—	25	47	90

Especificación	0.2 μm · 13 mm · pack 50	0.2 μm · 142 mm · pack 10	0.2 μm · 25 mm · pack 50	0.2 μm · 293 mm · pack 10	0.2 μm · 300 mm · pack 10	0.2 μm · 47 mm · pack 50	0.2 μm · 90 mm · pack 10	0.45 μm · 13 mm · pack 50	0.45 μm · 200 mm · pack 50	0.45 μm · 25 mm · pack 50	0.45 μm · 293 mm · pack 10	0.45 μm · 300 mm · pack 10	0.45 μm · 47 mm · pack 50	0.45 μm · 90 mm · pack 10	1 μm · 13 mm · pack 50	1 μm · 200 mm · pack 50	1 μm · 25 mm · pack 10	1 μm · 47 mm · pack 50	1 μm · 63.5 mm · pack 100	1 μm · 9.53 mm · pack 100	1 μm · 90 mm · pack 100	1 μm · 13 mm · pack 50	1 μm · 200 mm · pack 50	1 μm · 25 mm · pack 50	1 μm · 330 mm · pack 10	1 μm · 47 mm · pack 10	3 μm · 90 mm · pack 100	5 μm · 13 mm · pack 50	5 μm · 200 mm · pack 50	5 μm · 25 mm · pack 50	5 μm · 47 mm · pack 50	5 μm · 90 mm · pack 10	
Tamano de hoja	—	—	—	—	300 x 300	—	—	—	200 x 200	—	—	300 x 300	—	—	—	200 x 200	—	254 x 300	—	—	—	—	200 x 200	—	—	—	—	—	200 x 200	—	—	—	—
tamano	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	47 mm	—	—	—	—	—	

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)