



Sistemas de filtración WaterVac

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	190110-01	190120-01	190121-01	190210-01	190221-01
Tipo	[190110-01] Sistemas de filtración WaterVac (23 L/min 105 mbar)	—	[190121-01] Sistemas de filtración WaterVac (37 L/min 105 mbar)	[190210-01] Sistemas de filtración WaterVac (23 L/min 30 mbar)	[190221-01] Sistemas de filtración WaterVac (28 L/min 147 mbar)
potencia	DC24V, 1.8A or US Adaptor	DC24V, 1.8A or US Adaptor	DC24V, 1.8A or US Adaptor	DC24V, 1.8A or US Adaptor	DC24V, 1.8A or US Adaptor
max. vacío	313 mbar abs.	313 mbar abs.	313 mbar abs.	313 mbar abs.	313 mbar abs.
Caudal	4.5 L/min	4.5 L/min	4.5 L/min	4.5 L/min	4.5 L/min
motor	60W Brushless DC Motor	60W Brushless DC Motor	60W Brushless DC Motor	60W Brushless DC Motor	60W Brushless DC Motor
Nivel de ruido	60 dB	60 dB	60 dB	60 dB	60 dB
Espiga de manguera	ID8 (5/16 inch)	ID8 (5/16 inch)	ID8 (5/16 inch)	ID8 (5/16 inch)	ID8 (5/16 inch)
Material	(Watervac 200) Stainless steel, FKM, Silicone, PP, PPS (Watervac 100) Stainless steel, FKM, Silicone, PP, PA66	(Watervac 200) Stainless steel, FKM, Silicone, PP, PPS (Watervac 100) Stainless steel, FKM, Silicone, PP, PA66	(Watervac 200) Stainless steel, FKM, Silicone, PP, PPS (Watervac 100) Stainless steel, FKM, Silicone, PP, PA66	(Watervac 200) Stainless steel, FKM, Silicone, PP, PPS (Watervac 100) Stainless steel, FKM, Silicone, PP, PA66	(Watervac 200) Stainless steel, FKM, Silicone, PP, PPS (Watervac 100) Stainless steel, FKM, Silicone, PP, PA66
Adaptador	Spin-Lock	Spin-Lock	Spin-Lock	Spin-Lock	Spin-Lock
valvula placa	EPDM (Ethylene Propylene Diene Monomer)	EPDM (Ethylene Propylene Diene Monomer)	EPDM (Ethylene Propylene Diene Monomer)	EPDM (Ethylene Propylene Diene Monomer)	EPDM (Ethylene Propylene Diene Monomer)
fluido Path entrada	SS316	SS316	SS316	SS316	SS316
fluido path manguera	Silicone tubeâ	Silicone tubeâ	Silicone tubeâ	Silicone tubeâ	Silicone tubeâ
Junta torica	FKM	FKM	FKM	FKM	FKM

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)