



Pipeta electrónica

Código: N/D

Marca: Belltronic

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

The Electronic Pipette is a high-precision, user-friendly liquid handling device designed to enhance laboratory efficiency and accuracy.

Características

1. A motor drive digital control pipette with multifunction pipetting, mixing, stepper and dilution.
2. 2 buttons handle all operation and setting.
3. Light weight, ergonomic design, small body dimension for easy handling that guarantees fatigue free pipetting.
4. High accuracy, high performance stepper motor assures precision and repeatability and eliminates manual pipetting errors.
5. A wide range of pipetting modules for selection.
6. Adjustable speeds for aspiration and dispensing.
7. Li-ion battery and two charging mode enable longer operation time.
8. Self calibration-By link it to a PC and a balance with USB connector user can calibrate pipette by himself. No need to send it to the third party for calibration.

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	1	2	3	4
Rango de volumen	0,5-10µl	5-50µl	30-300 µl	100-1000µl
Incremento	0,01µl	0,1µl	1 µl	5µl
Volumen de prueba	10	50	300	1000
Inexactitud (1)	±0.10	±0.40	±1.8	±6.0
Inexactitud (2)	±1.0	±0.8	±0.6	±0.6
Precisión (1)	0.05	0.15	0.6	2.0
Precisión (2)	0.5	0.3	0.2	0.2

Aplicaciones

Use la guía para escoger la pipeta según volumen de trabajo, escala de ajuste y tolerancia visible en la tabla técnica. Seleccione cruzando Rango de volumen, Volumen de prueba; esos son los ejes que diferencian la cotización técnica.

01

Rango de volumen

Revise este eje con valores como 0,5-10 µl, 5-50 µl, 30-300 µl y 100-1000 µl.

02

Volumen de prueba

Revise este eje con valores como µl, 10, 1, 50, 5 y 300.

Cómo elegir rápido

Priorice el rango de volumen que cubre sus muestras reales y luego valide la precisión/error informado para ese rango. Confirme la variante por las especificaciones visibles antes de cotizar.

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)