



Componentes para membranas cerámicas TAMI

Código: N/D

Marca: STERLITECH

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Componentes para membranas cerámicas TAMI

Familia creada desde el catálogo vigente de Sterlitech para separar componentes y accesorios TAMI asociados a membranas cerámicas desde una plantilla histórica mixta.

SKU	Nombre proveedor	Fabricante	Fuente
ARACCDIS01	TAMI End fitting connection 4-6mm ribbed	TAMI	Ficha proveedor
ASPIR047E10	TAMI EPDM Spirals Disc-holder, 47mm, 10/Pk	TAMI	Ficha proveedor
ASPIR047S10	TAMI Silicon Spirals Disc-holder, 47mm, 10/Pk	TAMI	Ficha proveedor
ASPIR047V10	TAMI Viton Spirals Disc-holder, 47mm, 10/Pk	TAMI	Ficha proveedor
ASPIR090E10	TAMI EPDM Spirals Disc-holder, 90mm, 10/Pk	TAMI	Ficha proveedor
ASPIR090S10	TAMI Silicon Spirals Disc-holder, 90mm, 10/Pk	TAMI	Ficha proveedor
ASPIR090V10	TAMI Viton Spirals Disc-holder, 90mm, 10/Pk	TAMI	Ficha proveedor
AVIS04701	Screw Button Cell (47mm)	TAMI	Ficha proveedor
AVIS09001	Screw Button Cell (90mm)	TAMI	Ficha proveedor

Especificaciones técnicas

Todos bajo pedido por ahora. Filtra por poro, tamaño o pack para elegir el SKU.

Especificación	ARACCDIS01	ASPIR047E10	ASPIR047S10	ASPIR047V10	ASPIR090E10	ASPIR090S10	ASPIR090V10	AVIS04701	AVIS09001
----------------	------------	-------------	-------------	-------------	-------------	-------------	-------------	-----------	-----------

Especificación	ARACCDIS01	ASPIR047E10	ASPIR047S10	ASPIR047V10	ASPIR090E10	ASPIR090S10	ASPIR090V10	AVIS04701	AVIS09001
Tipo	[ARACCDIS01] Componentes para membranas cerámicas TAMI (ARACCDIS01)	[ASPIR047E10] Componentes para membranas cerámicas TAMI (ASPIR047E10)	[ASPIR047S10] Componentes para membranas cerámicas TAMI (ASPIR047S10)	[ASPIR047V10] Componentes para membranas cerámicas TAMI (ASPIR047V10)	[ASPIR090E10] Componentes para membranas cerámicas TAMI (ASPIR090E10)	[ASPIR090S10] Componentes para membranas cerámicas TAMI (ASPIR090S10)	[ASPIR090V10] Componentes para membranas cerámicas TAMI (ASPIR090V10)	[AVIS04701] Componentes para membranas cerámicas TAMI (AVIS04701)	[AVIS09001] Componentes para membranas cerámicas TAMI (AVIS09001)
Soporte	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel	316 Stainless Steel
Juntas toricas	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone	Viton, EPDM, or Silicone
Conexion de entrada	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter
Conexion de salida	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter	1/8" NPT female to 6mm Hose Barb Adapter
Presion	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)	4 bar (58 psi)
Tamano de filtro	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm	47 mm / 90 mm
Area de filtracion	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2	13.1 cm 2 / 56.3 cm 2
Temperatura de operacion	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)	<130 °C (<266 °F)

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)