

Portafiltros de vidrio y sets de vacio Rocker

Código: N/D

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Descripcion general

Portafiltros de vidrio y sets de vacio Rocker agrupados segun las fichas publicas de Sterlitech. La familia mantiene SKUs exactos del proveedor y separa variantes por producto y atributos visibles en la ficha fuente.

- Marca proveedor: Rocker.
- Variantes incluidas: 3.
- Fuente: fichas publicas de Sterlitech verificadas por URL individual.
- Seccion fuente detectada: Citations.
- Seccion fuente detectada: No results.
- Seccion fuente detectada: Ask An Expert.

Especificaciones técnicas

Familia Odoo	Portafiltros de vidrio y sets de vacio Rocker
Fichas fuente	6

167103-13

SKU Sterlitech	167103-13
Ficha del fabricante	Acero inoxidable Portafiltro Cover, SUS 316, 300mL (167103-13)
URL fuente	https://www.sterlitech.com/stainless-steel-filter-holder-cover-sus-316-300ml-167103-13.html

Datos visibles del fabricante

Acero inoxidable Portafiltro Cover, SUS 316, 300mL (167103-13) Portafiltro cover for 300 ml Acero inoxidable filter funnel. SKU: 167103-13
Brand: Rocker

167120-30

SKU Sterlitech	167120-30
Ficha del fabricante	Glass Portafiltro 300ml for VF3
URL fuente	https://www.sterlitech.com/catalog/product/view/id/10403/s/glass-filter-holder-300ml-for-vf3-167120-30/category/191/

Datos visibles del fabricante

Glass Portafiltro 300ml for VF3 SKU: 167120-30 Brand: Rocker

Contenido visible del fabricante

Specifications Filter Size (mm) 25 25 47 47 47 47 90 90 90 Model No. VF5 VF8 VF6 VF7 VF3 VF12 VF15 VF16 VF17 Brand Rocker Rocker

Rocker Rocker Rocker Rocker Rocker Rocker Rocker Support Material Sintered glass SS with PTFE gasket Sintered glass SS with PTFE gasket Sintered glass Sintered glass SS316 Sintered glass Sintered glass Funnel Capacity (ml) 15 15 300 300 300 300 1000 1000 1000 Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper Material Silicone stopper Silicone stopper Silicone stopper Silicone stopper N/A Silicone stopper Silicone stopper Silicone stopper GL45 Filtration Adaptor Material N/A N/A N/A N/A N/A PP (autoclavable) PP (autoclavable) PP (autoclavable) Clamp Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Filtration area (cm2) 3.1 2.5 13.2 9.6 13.2 13.2 40.6 40.6 40.6 Flask Capacity (ml) 125 125 1000 1000 1000 1000 5000 5000 3500 Flask Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass KG, KGS, KGT, and GF Models Filter size (mm) 13 (will accept 25 mm) 25 47 90 13(will accept 25 mm) 25 Brand Advantec Advantec Advantec Advantec Sterlitech Sterlitech Support Material Sintered glass Sintered glass Sintered glass Sintered glass Sintered glass Sintered glass Stainless steel PTFE Sintered glass Stainless steel Glass Frit Glass Frit Funnel Capacity 13/100, 100, 500, 1000 mL 15, 150, 300 mL 100, 300, 500, 1000 mL 1000 mL 100ml 300ml Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 250ml filtering flask #8 Silicone rubber for 1 L flask Clamp Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Filtration area (cm²) 1.2 2.1 9.6 43 1.2 2.1 Applications DNA/RNA and protein filtration Gravimetric analyses Sterility and microbial testing, colony counting Solvent purification and filtration

Tabla fuente 1

Tamaño de filtro (mm)	25	25	47	47	47	47	90	90	90
Model No.	VF5	VF8	VF6	VF7	VF3	VF12	VF15	VF16	VF17
Brand	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker
Support Material	Sintered glass	SS with PTFE gasket	Sintered glass	SS with PTFE gasket	Sintered glass	Sintered glass	SS316	Sintered glass	Sintered glass
Funnel Capacity (ml)	15	15	300	300	300	300	1000	1000	1000
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper Material	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper	N/A	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper
GL45 Filtration Adaptor Material	N/A	N/A	N/A	N/A	N/A	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)
Clamp	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Filtration area (cm ²)	3.1	2.5	13.2	9.6	13.2	13.2	40.6	40.6	40.6
Flask Capacity (ml)	125	125	1000	1000	1000	1000	5000	5000	3500
Flask Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass

Tabla fuente 2

	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models
Tamaño de filtro (mm)	13 (will accept 25 mm)	25	47	90	13(will accept 25 mm)	25
Brand	Advantec	Advantec	Advantec	Advantec	Sterlitech	Sterlitech
Support Material	Sintered glass	Sintered glass Acero inoxidable	Sintered glass Acero inoxidable PTFE	Sintered glass Acero inoxidable	Glass Frit	Glass Frit
Funnel Capacity	13/100, 100, 500, 1000 mL	15, 150, 300 mL	100, 300, 500, 1000 mL	1000 mL	100ml	300ml
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 250ml filtering flask	#8 Silicone rubber for 1 L flask

Clamp	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum
Filtration area (cm 2)	1.2	2.1	9.6	43	1.2	2.1

167120-31

SKU Sterlitech	167120-31
Ficha del fabricante	Glass Portafiltro 300ml for VF12/VF6
URL fuente	https://www.sterlitech.com/glass-filter-holder-300ml-for-vf16-167120-31.html

Datos visibles del fabricante

Glass Filter Holder 300ml for VF12/VF6 SKU: 167120-31 Brand: Rocker Funnel Size: 300 mL

Contenido visible del fabricante

Specifications Filter Size (mm) 25 25 47 47 47 47 90 90 90 Model No. VF5 VF8 VF6 VF7 VF3 VF12 VF15 VF16 VF17 Brand Rocker Rocker Rocker Rocker Rocker Rocker Support Material Sintered glass SS with PTFE gasket Sintered glass SS with PTFE gasket Sintered glass Sintered glass SS316 Sintered glass Sintered glass Funnel Capacity (ml) 15 15 300 300 300 300 1000 1000 1000 Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper Material Silicone stopper Silicone stopper Silicone stopper Silicone stopper Silicone stopper N/A Silicone stopper Silicone stopper Silicone stopper GL45 Filtration Adaptor Material N/A N/A N/A N/A N/A PP (autoclavable) PP (autoclavable) PP (autoclavable) PP (autoclavable) Clamp Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Filtration area (cm2) 3.1 2.5 13.2 9.6 13.2 13.2 40.6 40.6 40.6 Flask Capacity (ml) 125 125 1000 1000 1000 1000 5000 5000 3500 Flask Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass KG, KGS, KGT, and GF Models Filter size (mm) 13 (will accept 25 mm) 25 47 90 13(will accept 25 mm) 25 Brand Advantec Advantec Advantec Advantec Sterlitech Sterlitech Support Material Sintered glass Sintered glass Stainless steel Sintered glass Stainless steel PTFE Sintered glass Stainless steel Glass Frit Glass Frit Funnel Capacity 13/100, 100, 500, 1000 mL 15, 150, 300 mL 100, 300, 500, 1000 mL 1000 mL 100ml 300ml Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 250ml filtering flask #8 Silicone rubber for 1 L flask Clamp Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Filtration area (cm 2) 1.2 2.1 9.6 43 1.2 2.1 Applications DNA/RNA and protein filtration Gravimetric analyses Sterility and microbial testing, colony counting Solvent purification and filtration

Tabla fuente 1

Tamaño de filtro (mm)	25	25	47	47	47	47	90	90	90
Model No.	VF5	VF8	VF6	VF7	VF3	VF12	VF15	VF16	VF17
Brand	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker
Support Material	Sintered glass	SS with PTFE gasket	Sintered glass	SS with PTFE gasket	Sintered glass	Sintered glass	SS316	Sintered glass	Sintered glass
Funnel Capacity (ml)	15	15	300	300	300	300	1000	1000	1000
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper Material	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper	N/A	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper
GL45 Filtration Adaptor Material	N/A	N/A	N/A	N/A	N/A	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)
Clamp	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Filtration area (cm2)	3.1	2.5	13.2	9.6	13.2	13.2	40.6	40.6	40.6
Flask Capacity (ml)	125	125	1000	1000	1000	1000	5000	5000	3500
Flask Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass

Tabla fuente 2

	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models
Tamaño de filtro (mm)	13 (will accept 25 mm)	25	47	90	13(will accept 25 mm)	25
Brand	Advantec	Advantec	Advantec	Advantec	Sterlitech	Sterlitech
Support Material	Sintered glass	Sintered glass Acero inoxidable	Sintered glass Acero inoxidable PTFE	Sintered glass Acero inoxidable	Glass Frit	Glass Frit
Funnel Capacity	13/100, 100, 500, 1000 mL	15, 150, 300 mL	100, 300, 500, 1000 mL	1000 mL	100ml	300ml
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 250ml filtering flask	#8 Silicone rubber for 1 L flask
Clamp	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum
Filtration area (cm 2)	1.2	2.1	9.6	43	1.2	2.1

167120-38

SKU Sterlitech	167120-38
Ficha del fabricante	Glass Portafiltro 1000ml for VF16, VF17
URL fuente	https://www.sterlitech.com/glass-filter-holder-1000ml-for-rocker-vf16-vf17.html

Datos visibles del fabricante

Glass Filter Holder 1000ml for VF16, VF17 SKU: 167120-38 Brand: Rocker Funnel Size: 1000 mL

Contenido visible del fabricante

Specifications Filter Size (mm) 25 25 47 47 47 47 90 90 90 Model No. VF5 VF8 VF6 VF7 VF3 VF12 VF15 VF16 VF17 Brand Rocker Rocker Rocker Rocker Rocker Rocker Rocker Support Material Sintered glass SS with PTFE gasket Sintered glass SS with PTFE gasket Sintered glass Sintered glass SS316 Sintered glass Sintered glass Funnel Capacity (ml) 15 15 300 300 300 300 1000 1000 1000 Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper Material Silicone stopper Silicone stopper Silicone stopper Silicone stopper N/A Silicone stopper Silicone stopper Silicone stopper Silicone stopper GL45 Filtration Adaptor Material N/A N/A N/A N/A N/A PP (autoclavable) PP (autoclavable) PP (autoclavable) PP (autoclavable) Clamp Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Filtration area (cm2) 3.1 2.5 13.2 9.6 13.2 13.2 40.6 40.6 40.6 Flask Capacity (ml) 125 125 1000 1000 1000 1000 5000 5000 3500 Flask Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass KG, KGS, KGT, and GF Models Filter size (mm) 13 (will accept 25 mm) 25 47 90 13(will accept 25 mm) 25 Brand Advantec Advantec Advantec Advantec Sterlitech Sterlitech Support Material Sintered glass Sintered glass Stainless steel Sintered glass Stainless steel PTFE Sintered glass Stainless steel Glass Frit Glass Frit Funnel Capacity 13/100, 100, 500, 1000 mL 15, 150, 300 mL 100, 300, 500, 1000 mL 1000 mL 100ml 300ml Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 250ml filtering flask #8 Silicone rubber for 1 L flask Clamp Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Filtration area (cm 2) 1.2 2.1 9.6 43 1.2 2.1 Applications DNA/RNA and protein filtration Gravimetric analyses Sterility and microbial testing, colony counting Solvent purification and filtration

Tabla fuente 1

Tamaño de filtro (mm)	25	25	47	47	47	47	90	90	90
Model No.	VF5	VF8	VF6	VF7	VF3	VF12	VF15	VF16	VF17
Brand	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker

Support Material	Sintered glass	SS with PTFE gasket	Sintered glass	SS with PTFE gasket	Sintered glass	Sintered glass	SS316	Sintered glass	Sintered glass
Funnel Capacity (ml)	15	15	300	300	300	300	1000	1000	1000
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper Material	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper	N/A	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper
GL45 Filtration Adaptor Material	N/A	N/A	N/A	N/A	N/A	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)
Clamp	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Filtration area (cm2)	3.1	2.5	13.2	9.6	13.2	13.2	40.6	40.6	40.6
Flask Capacity (ml)	125	125	1000	1000	1000	1000	5000	5000	3500
Flask Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass

Tabla fuente 2

	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models
Tamaño de filtro (mm)	13 (will accept 25 mm)	25	47	90	13(will accept 25 mm)	25
Brand	Advantec	Advantec	Advantec	Advantec	Sterlitech	Sterlitech
Support Material	Sintered glass	Sintered glass Acero inoxidable	Sintered glass Acero inoxidable PTFE	Sintered glass Acero inoxidable	Glass Frit	Glass Frit
Funnel Capacity	13/100, 100, 500, 1000 mL	15, 150, 300 mL	100, 300, 500, 1000 mL	1000 mL	100ml	300ml
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 250ml filtering flask	#8 Silicone rubber for 1 L flask
Clamp	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum
Filtration area (cm 2)	1.2	2.1	9.6	43	1.2	2.1

167200-07

SKU Sterlitech	167200-07
Ficha del fabricante	VF7, Glass Filtration Set, includes 300mL/47mm Glass Filter Holder, No. 8 Stopper, 1L Receiver Flask, and Silicone Fixing Sucker
URL fuente	https://www.sterlitech.com/vf7-glass-filtration-set.html

Datos visibles del fabricante

VF7, Glass Filtration Set, includes 300mL/47mm Glass Portafiltro, No. 8 Stopper, 1L Receiver Flask, and Silicone Fixing Sucker Glass Portafiltro assembly with suctioned base for added stability and safety. Acero inoxidable membrane support screen with PTFE seal is easily cleaned and reused. Ideal for solvent purification and general filtration for microbiology, suspended solid analysis etc. SKU: 167200-07
Brand: Rocker Material Type: Acero inoxidable Funnel Size: 300mL Filter Area: 47mm

Contenido visible del fabricante

Specifications Filter Size (mm) 25 25 47 47 47 47 90 90 90 Model No. VF5 VF8 VF6 VF7 VF3 VF12 VF15 VF16 VF17 Brand Rocker Rocker Rocker Rocker Rocker Rocker Rocker Support Material Sintered glass SS with PTFE gasket Sintered glass SS with PTFE gasket Sintered glass Sintered glass SS316 Sintered glass Sintered glass Funnel Capacity (ml) 15 15 300 300 300 300 1000 1000 1000 Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Stopper Material Silicone stopper Silicone stopper Silicone stopper Silicone stopper Silicone stopper N/A Silicone stopper Silicone stopper Silicone stopper Silicone stopper GL45 Filtration Adaptor Material N/A N/A N/A N/A N/A PP (autoclavable) PP (autoclavable)

PP (autoclavable) PP (autoclavable) Clamp Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum Aluminum
Filtration area (cm²) 3.1 2.5 13.2 9.6 13.2 13.2 40.6 40.6 40.6 Flask Capacity (ml) 125 125 1000 1000 1000 1000 5000 5000 3500 Flask
Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass
Borosilicate glass Borosilicate glass KG, KGS, KGT, and GF Models Filter size (mm) 13 (will accept 25 mm) 25 47 90 13(will accept 25 mm)
25 Brand Advantec Advantec Advantec Advantec Sterlitech Sterlitech Support Material Sintered glass Sintered glass Stainless steel Sintered
glass Stainless steel PTFE Sintered glass Stainless steel Glass Frit Glass Frit Funnel Capacity 13/100, 100, 500, 1000 mL 15, 150, 300 mL
100, 300, 500, 1000 mL 1000 mL 100ml 300ml Funnel Material Borosilicate glass Borosilicate glass Borosilicate glass Borosilicate glass
Borosilicate glass Borosilicate glass Stopper #5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask #5 Silicone rubber for 125 mL
flask Optional #8b for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 1 L flask #8 Silicone rubber for 250ml filtering flask #8
Silicone rubber for 1 L flask Clamp Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum Anodized aluminum
Anodized aluminum Filtration area (cm²) 1.2 2.1 9.6 43 1.2 2.1 Applications DNA/RNA and protein filtration Gravimetric analyses Sterility
and microbial testing, colony counting Solvent purification and filtration

Tabla fuente 1

Tamaño de filtro (mm)	25	25	47	47	47	47	90	90	90
Model No.	VF5	VF8	VF6	VF7	VF3	VF12	VF15	VF16	VF17
Brand	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker	Rocker
Support Material	Sintered glass	SS with PTFE gasket	Sintered glass	SS with PTFE gasket	Sintered glass	Sintered glass	SS316	Sintered glass	Sintered glass
Funnel Capacity (ml)	15	15	300	300	300	300	1000	1000	1000
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper Material	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper	N/A	Silicone stopper	Silicone stopper	Silicone stopper	Silicone stopper
GL45 Filtration Adaptor Material	N/A	N/A	N/A	N/A	N/A	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)	PP (autoclavable)
Clamp	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum	Aluminum
Filtration area (cm ²)	3.1	2.5	13.2	9.6	13.2	13.2	40.6	40.6	40.6
Flask Capacity (ml)	125	125	1000	1000	1000	1000	5000	5000	3500
Flask Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass

Tabla fuente 2

	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models	KG, KGS, KGT, and GF Models
Tamaño de filtro (mm)	13 (will accept 25 mm)	25	47	90	13(will accept 25 mm)	25
Brand	Advantec	Advantec	Advantec	Advantec	Sterlitech	Sterlitech
Support Material	Sintered glass	Sintered glass Acero inoxidable	Sintered glass Acero inoxidable PTFE	Sintered glass Acero inoxidable	Glass Frit	Glass Frit
Funnel Capacity	13/100, 100, 500, 1000 mL	15, 150, 300 mL	100, 300, 500, 1000 mL	1000 mL	100ml	300ml
Funnel Material	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass	Borosilicate glass
Stopper	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#5 Silicone rubber for 125 mL flask Optional #8b for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 1 L flask	#8 Silicone rubber for 250ml filtering flask	#8 Silicone rubber for 1 L flask
Clamp	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum	Anodized aluminum
Filtration area (cm ²)	1.2	2.1	9.6	43	1.2	2.1

167320-30

SKU Sterlitech	167320-30
Ficha del fabricante	Conversion Kit, Rocker 300 to 320 or Rocker 500 to 520
URL fuente	https://www.sterlitech.com/rocker-300-to-320-conversion-kit-167320-30.html

Datos visibles del fabricante

Conversion Kit, Rocker 300 to 320 or Rocker 500 to 520 SKU: 167320-30 Brand: Rocker

Aplicaciones

Guia de seleccion

Seleccione la variante comparando los atributos que cambian dentro de esta familia.

Poro: revise 1000 mL, 300 mL, 300mL antes de cotizar.

Si la ficha corresponde a un repuesto o accesorio, valide compatibilidad con el equipo o portafiltro antes de confirmar la compra.

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)