

Rotor angular 12 x 2.0/1.5 ml para centrifuga de mesa refrigerada de alta velocidad

Código: B2-01-010434-R02

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Angle Rotor

Especificaciones técnicas

Especificación	-R02
Rotor	Rotor angular
Velocidad máxima (rpm)	20000
Fuerza centrífuga relativa (xg)	27000
Capacidad	12*2.0/1.5ml
Dimensión del tubo (mm)	Φ10*42

Aplicaciones

1. Confirm the capacity you need

Compare the number and volume of tubes you need to process with the rotor capacity. Check that the diameter and length of your tube match the stated dimension.

- **Capacity:** 12*2.0/1.5ml
- **Dimension of Tube (mm):** Φ10*42

2. Check the working speed

Check that the maximum speed and relative centrifugal force cover what your protocol requires.

- **Max. Speed(rpm):** 20000
- **RCF (xg):** 27000

3. Verify compatibility with the centrifuge

Confirm that the rotor type is compatible with the centrifuge where it will be installed.

- **Rotor:** Angle Rotor

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)