

Rotor angular 6 x 50 ml, tubo de 29 x 106 mm, para centrifuga de mesa de alta velocidad, 12000 rpm

Código: B2-01-012469-R07

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Angle Rotor

Especificaciones técnicas

Especificación	-R07
Tipo de rotor	Rotor angular
Velocidad máxima (rpm)	12000
Fuerza centrífuga relativa máxima (xg)	15130
Capacidad	6*50ml, tubo de fondo redondo
Dimensión del tubo (mm)	ø29*106

Aplicaciones

1. Capacity and tubes

Compare the rotor capacity with the number of tubes and the volume you process in each cycle.

- **Capacity:** 6*50ml(●)

2. Speed and centrifugal force

Check that the maximum speed and the maximum relative centrifugal force cover your sample protocol.

- **Max Speed(rpm):** 12000
- **Max RCF(xg):** 15130

3. Centrifuge compatibility

Confirm that the rotor type matches the table-top centrifuge where you will install it.

- **Rotor:** Angle Rotor

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)