

Rotor oscilante 4 x 50 ml para centrifuga de piso de baja velocidad

Código: B2-01-012213-R12

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Swing Rotor

Especificaciones técnicas

Especificación	-R12
Tipo de rotor	Rotor oscilante
Volumen	4*50ml
Velocidad máxima (rpm)	4500
Fuerza centrífuga relativa máxima (xg)	3962
Adaptadores	50ml(▲), 20ml, 15ml, 10ml, 5ml, 1.5/2ml

Aplicaciones

1. Confirm the rotor capacity

Compare the number of tubes and the volume you process per run with the rotor capacity.

- **Volume:** 4*50ml

Check that the rotor type matches the centrifuge you own or plan to acquire.

- **Rotors Type:** Swing Rotor

2. Review the speed and centrifugal force

Confirm that the maximum speed and relative centrifugal force of the rotor cover what your separation protocol requires.

- **Max. Speed(rpm):** 4500
- **Max. RCF(xg):** 3962

3. Choose the adapters for your tubes

Review which adapters the rotor accepts and order the ones that match the tubes you use.

- **Adapters:** 50ml(▲), 20ml, 15ml, 10ml, 5ml, 1.5/2ml

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)