

Rotor oscilante para microplacas 4 x 2 x 96 pocillos para centrifuga de piso de baja velocidad

Código: B2-01-012213-R29

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Swing Microplate Rotor

Especificaciones técnicas

Especificación	-R29
Tipo de rotor	Rotor oscilante para microplacas
Volumen	4*2*96 pocillos
Velocidad máxima (rpm)	4000
Fuerza centrífuga relativa máxima (xg)	2987
Adaptadores	—

Aplicaciones

1. Capacity and plates

Confirm how many microplates you process per run and their format, and compare it with the rotor capacity.

- **Volume:** 4*2*96 well

2. Speed and centrifugal force

Compare the speed and relative centrifugal force your protocol requires with the rotor maximums.

- **Max. Speed(rpm):** 4000
- **Max. RCF(xg):** 2987

3. Centrifuge compatibility

Verify that your floor-standing low-speed centrifuge accepts this microplate rotor before buying it.

- **Rotors Type:** Swing Microplate Rotor

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)