

Rotor angular 6 x 50 ml para centrifuga de piso de baja velocidad

Código: B2-01-012213-R38

Marca: N/D

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Angle Rotor

Especificaciones técnicas

Especificación	-R38
Tipo de rotor	Rotor angular
Volumen	6*50ml
Velocidad máxima (rpm)	6000
Fuerza centrífuga relativa máxima (xg)	3904
Adaptadores	50ml(▲), 20ml, 15ml, 10ml, 5ml, 1.5/2ml

Aplicaciones

1. Confirm tube capacity

Compare the number and volume of tubes you process per run with the rotor capacity.

- **Volume:** 6*50ml

2. Check speed and centrifugal force

Check that your protocol does not require a speed or relative centrifugal force above the rotor maximums.

- **Max. Speed(rpm):** 6000
- **Max. RCF(xg):** 3904

3. Check adapters and centrifuge

Confirm that the tubes you use match the adapters listed for this rotor.

- **Adapters:** 50ml(▲), 20ml, 15ml, 10ml, 5ml, 1.5/2ml

Check that your centrifuge accepts this rotor type before purchase.

- **Rotors Type:** Angle Rotor

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)