



Ventilador Minneapolis Blower Door™ Modelo 3 con Anillos y Controlador

Código: BD3FAN

Marca: The Energy Conservatory

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle Detalle técnico

Description Model 3 Blower Door Fan with Flow Rings and Fan Speed Controller The Model 3 Blower Door Fan moves air to pressurize or depressurize a building during a building envelope test. Features AC 110 volt, 3/4 horse power motor Flow sensor measures air flow through the fan Lightweight and rugged injection molded fan housing Top handle for transportation Flow rings A and B included, measure air flows down to 300 CFM (Optional rings C, D and E, sold separately, can measure to 11 CFM) The variable fan speed controller helps supply power to the fan and can be used with 110 volt/60 hertz or 220 volt/50 hertz AC power grids Color coded interior LED indicator for operation status or trouble shooting Fan speed control jack used to control fan speed during automated testing or using TEC's digital gauge cruise control function (Fan control cable sold separately) Belt clip on the controller...

Marca: The Energy Conservatory. **Proveedor:** THE ENERGY CONSERVATORY INC..

Especificaciones técnicas

Compara modelos principales con especificaciones tecnicas validadas.

Especificación	Accesorio o componente TEC - Componentes (Ventiladores/Controles)
Tipo de producto	Accesorio o componente TEC
Subfamilia Cotecno	Componentes (Ventiladores/Controles)
Línea TEC	Minneapolis Blower Door™ / Accesorios Minneapolis Blower Door™
Peso declarado por proveedor	1 lbs
Documentación disponible	Formulario de servicio de equipo;

Aplicaciones

- Configuración de sistemas TEC
- Montaje o conexión de equipos
- Soporte de ensayos de hermeticidad

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)