



Sistema Minneapolis Duct Blaster® con Medidor DG-1000

Código: DUCT-KIT-001

Marca: The Energy Conservatory

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

Detalle

Detalle técnico

Description Minneapolis Duct Blaster® System with DG-1000 The Minneapolis Duct Blaster® is a calibrated air flow measurement system designed to test and document the airtightness of forced air duct systems in both houses and light commercial buildings. Minneapolis Duct Blaster® System Features Provides quick and accurate airtightness measurements from 10 – 1,500 CFM Compatible for both pressurization and depressurization testing Lightweight fan weighs only 7 pounds Ideal for use in new construction applications where a Blower Door can't be used (e.g. before sheet rock is installed) Use to certify code compliance for total duct leakage and duct leakage to the outside as in IECC 2009 and 2012 DG-1000 Digital Pressure and Flow Gauge Features High Resolution Touch Screen: Gives you improved visibility and usability with the touch of your finger Intelligent Micro-Processor: Puts the power of...

Marca: The Energy Conservatory. **Proveedor:** THE ENERGY CONSERVATORY INC..

Especificaciones técnicas

Compara modelos principales con especificaciones técnicas validadas.

Especificación	Sistema o kit de ensayo - Manómetros Digitales - IECC 2009
Tipo de producto	Sistema o kit de ensayo
Subfamilia Cotecno	Manómetros Digitales
Línea TEC	Minneapolis Duct Blaster® / Kits Minneapolis Duct Blaster®
Peso declarado por proveedor	29 lbs
Documentación disponible	Formulario de servicio de equipo; Folleto general; Documento de referencia;
Normas/certificaciones declaradas	IECC 2009

Aplicaciones

- Medición de presión
- Lectura de caudal
- Registro de datos de ensayo

Siguiente paso: [ver producto en Cotecno](#) | [solicitar cotización](#)