



## Bandeja de Presión - 12x14x4

**Código:** PRESSPAN

**Marca:** The Energy Conservatory

[Ver producto en Cotecno](#) | [Solicitar cotización](#)

[Detalle](#) | [Especificaciones](#) | [Aplicaciones](#)

## Detalle

### Detalle técnico

Description Pressure Pan 12"x14"x4" The Pressure Pan is a duct leakage diagnostic tool which is used along with the Blower Door and digital pressure gauge to identify exterior air leaks in forced air duct systems. It is most effective when a significant portion of the duct system is located outside the conditioned house space (e.g. attics, crawlspaces, garages). Generally, the higher the pressure pan reading, the leakier that part of the duct system is to the outside. Pressure pans do not directly measure leakage rates. Rather, a pressure pan is used to measure the pressure difference between the house and a duct run during a Blower Door test. This pressure reading can be used to estimate the degree to which a particular duct run is connected to the outside. Features Flexible gasket around the opening of the pan helps create a seal around the registers while taking the pressure reading....

**Marca:** The Energy Conservatory. **Proveedor:** THE ENERGY CONSERVATORY INC..

## Especificaciones técnicas

Compara modelos principales con especificaciones tecnicas validadas.

| Especificación               | Sistema o kit de ensayo - Accesorios / Bandejas de Presión |
|------------------------------|------------------------------------------------------------|
| Tipo de producto             | Sistema o kit de ensayo                                    |
| Subfamilia Cotecno           | Accesorios / Bandejas de Presión                           |
| Línea TEC                    | Pressure Pan / Pressure Pan Kits                           |
| Peso declarado por proveedor | 1                                                          |
| Documentación disponible     | Formulario de servicio de equipo;                          |

## Aplicaciones

- Configuración de sistemas TEC
- Montaje o conexión de equipos
- Soporte de ensayos de hermeticidad

**Siguiente paso:** [ver producto en Cotecno](#) | [solicitar cotización](#)