

CLÁSICO



SKU: N / A | **Categorías:** [Thies Clima](#), [Viento](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"]
[vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[vc_column_text]El transmisor de viento Classic garantiza una alta precisión de medición permanente en condiciones extremas y goza de una excelente reputación entre los usuarios profesionales de dichos instrumentos, por ejemplo, los científicos del Servicio Meteorológico Alemán. A lo largo de los años, se han perfeccionado para convertirlos en productos de alta calidad, con datos estandarizados y conexiones de enchufe.[/vc_column_text]
[/vc_column_inner column_margin="default" text_align="left" css=".vc_custom_1597668708409{border-radius: 2px !important;}"]
[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[vc_column_text]

Imagen

[/vc_column_text][/vc_column_inner]
[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[vc_column_text]

Nombre del Producto

[/vc_column_text][/vc_column_inner]
[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[vc_column_text]

Descripción corta

[/vc_column_text][/vc_column_inner][/vc_row_inner]
[vc_row_inner column_margin="default" text_align="left"]
[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[image_with_animation image_url="138427" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]
[/vc_column_inner]
[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]
[vc_column_text]

4.3105.22.000[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]El transmisor de viento está diseñado para la medición independiente de la dirección del flujo de aire horizontal con generador de CC.

- Salida: generador DC

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-clasico/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138427" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [/vc_column_text]

Transmisor de dirección del viento Classic

4.3120.22.xxx[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]Transmisor de valores de medición para medir la dirección del flujo de aire horizontal

- Salida del potenciómetro

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-clasico/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138427" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [/vc_column_text]

Transmisor de dirección del viento Classic

4.3121.33.000[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]Transmisor de valores de medición para medir la dirección de la

- Salida digital de flujo de aire horizontal (8 bits en paralelo)

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-clasico-2/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138427" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [/vc_column_text]

Transmisor de dirección del viento Classic

4.3125.33.100[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]Transmisor de valores de medición para medir la dirección de la

- Salida digital de flujo de aire horizontal (serie sincronizada de 8 bits)

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-clasico-3/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138427" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [/vc_column_text]

bg_image_animation="none"] [vc_column_text] Transmisor de dirección del viento Classic
4.3125.33.xxx [vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de valores de medición para medir la dirección del flujo de aire horizontal y salida

- Analógica salida analógica

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-clasico-4/" [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138431" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento Classic
4.3303.22.xxx [vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] El transmisor de viento está diseñado para la medición independiente de la dirección del flujo de aire horizontal.

- Salida analógica / digital

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-classic/" [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado
4.3324.32.000 [vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"

tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.
Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión estándar
- Velocidad del viento: salida de frecuencia
- Dirección del viento: paralelo de 8 bits

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-2/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado 4.3324.32.001 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.

Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento de la

- Versión de barco de flujo de aire horizontal
- Velocidad del viento de salida: salida de frecuencia
- Dirección del viento de salida: paralelo de 8 bits

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-5/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado 4.3324.32.xxx [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión estándar
- Velocidad del viento: salida analógica
- Dirección del viento: salida analógica

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-6/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado 4.3336.22.000 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.

Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión estándar
- Velocidad del viento: salida de frecuencia
- Dirección del viento: sincronismo en serie

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-3/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado 4.3336.32.001 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]



tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.
Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión de barco
- Velocidad del viento: salida de frecuencia
- Dirección del viento: sincronismo en serie

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-4/"] [/vc_column_inner] [/vc_row_inner]

[/vc_column] [/vc_row]

COTECNO