

## EATON LOFPLEAT AG LPAG-40-1-4S FILTER CARTRIDGE



**SKU:** LPAG-40-1-4S DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

## DESCRIPCIÓN DEL PRODUCTO

### EATON LOFPLEAT AG LPAG-40-1-4S FILTER CARTRIDGE

**PART NUMBER: LPAG-40-1-4S**

[Please contact us for more information and/or a quotation request.](#)

#### Specifications

|                 |                   |
|-----------------|-------------------|
| Brand           | Eaton LOFPLEAT AG |
| Model           | LPAG 40 1 4S      |
| Pore Size $\mu$ | 1                 |

#### Dimensions / Weights

|                   |           |
|-------------------|-----------|
| Length in inch    | 40.0      |
| Length in cm      | 101.6     |
| Quantity per case | 12 pieces |



[Download Datasheet](#)



## LOFPLEAT AG SERIES CARTRIDGE FILTERS

Get absolute efficiency with this cost-effective all polypropylene cartridge. The pleated design provides a large surface area for long lasting filtration efficiency.

#### Features / Benefits

- Fits broad application range with 0.2 to 100 micron retention
- Acceptable for food and beverage applications

- Meets USP Class VI biological tests for plastics
- Beta rating of 5000, 99.98% efficiency
- High flow and long life for minimum maintenance
- Available in lengths up to 40 inches
- Eliminates dirt unloading at high differential pressures due to fixed pore structure

## **Filter Specifications**

### **Media**

- Polypropylene

#### **Inner core**

- Polypropylene

#### **End caps**

- Polypropylene

#### **Cage**

- Polypropylene

#### **Gaskets/O-Rings options**

- Buna-N, EPDM, Silicone, Viton®, FEP encapsulated Viton (O-Rings only)

#### **Micron ratings**

- 0.2, 0.45, 1.0, 2.5, 5.0, 10, 25, 50, 100 µm

#### **Typical Applications**

- process applications
- chemicals

## INFORMACIÓN ADICIONAL

|         |                                                                                                                                                                                                                                   |
|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| url_fab | <a href="https://www.lenntech.com/products/Eaton-LOFPLEAT-AG/LPAG-40-1-4S/LPAG-40-1-4S-Filter-Cartridge/index.html">https://www.lenntech.com/products/Eaton-LOFPLEAT-AG/LPAG-40-1-4S/LPAG-40-1-4S-Filter-Cartridge/index.html</a> |
| brand   | Lenntech                                                                                                                                                                                                                          |

COTECNO