

FILTRACIÓN ALFAWATER



SKU: N / A | **Categorías:** [Filtración alfawater](#), [Filtros de sedimentos](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"]/[tabbed_section][vc_column_text]Alfawater crea soluciones de tratamiento de agua y tiene una vasta experiencia en el diseño y fabricación de filtros manuales, autolimpiantes y automáticos. Alfawater desarrolla soluciones de filtración de vanguardia que satisfacen las necesidades de aplicaciones industriales y no industriales.[/vc_column_text][vc_column_text]

Filtros manuales

[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

- [Serie ABG](#)
- [Serie ABK](#)
- [Serie AHC](#)
- [Serie AMB](#)
- [Serie ASF](#)

[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159426" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

Filtros automáticos

- [Serie ABF](#)
- [Serie ABR](#)
- [Serie ABV](#)
- [Serie AMA](#)
- [Serie AVB](#)
- [Serie AVC](#)
- [AVC en filtro GRP](#)

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="159427" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_row_inner]
```

```
[vc_column_text]
```

- Descripción general de la filtración Alfawater

```
[/vc_column_text][vc_column][vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO