

FILTROS LENNBAG



SKU: N / A | **Categorías:** [Filtros LennBag](#), [Lenntech](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"] [/tabbed_section] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" width="1/3" column_shadow="none" column_border_radius="none" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Bolsa de filtro de alto rendimiento

- [LennBag HE](#)

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] **Bolsa de filtro de monofilamento**

- [LennBag NMO - PEMO - POMO - T](#)

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="158815" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [/vc_row_inner] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] **Bolsa de filtro de aguja**

[LennBag PO - PE - N - PTFE - PPS - HT](#)

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] **Bolsa de filtro de alta eficiencia**

- [LennBag PP95](#)

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none">[vc_column_text]**Bolsa de filtro de alta eficiencia**

- [LennBag PP95](#)

[/vc_column_text][/vc_column_inner][/vc_row_inner]

[vc_column_text]

Descripción General

- [LennHFP](#)
- [Carcasas LennBag](#)
- [Descripción General De Los Filtros Lennbag](#)

[/vc_column_text][/vc_column][/vc_row]



INFORMACIÓN ADICIONAL

COTECNO