

HARMSCO HOUSING HP HUR 170 HP FILTER HOUSING



SKU: HP HUR 170 HP P | **Categorías:** [Equipo Analítico](#) |

DESCRIPCIÓN DEL PRODUCTO

HARMSCO HOUSING HP HUR 170 HP FILTER HOUSING

Part Number: HP HUR 170 HP P



Especificaciones

Marca	Harmsco Housing HP
Tipo	for Polyester Cartridge
Presión de trabajo bar	10.3
Presión psi	150
Temperatura máxima de °C	60
Temperatura máxima de °F	140
Área de medios ft ²	170
Flujo gpm	150
Flujo l/min	up to 568
Flujo m ³ /h	up to 36
Conexión de drenaje - pulgadas	1 NPT
Material	304 Stainless Steel
O-Ring / juntas /	EPDM

Dimensiones / Pesos

Entrada inch	2
Salida pulgadas	2
Longitud del cartucho inch	30/3/4
diámetro exterior pulgada	Ø7-3/4
Altura pulgadas	40-1/2
Peso kg	29
Peso lb	64
Cantidad por caja	1 piezas
Aplicación	Drinking water, Process water, Industrial water, RO Pre-Filtration, Coolig Tower, Surface water



Lower Operation Cost

Harmsco® HP Hurricane® filters provide unsurpassed performance.

Our unique design separates dense solids prior to cartridge filtration for extended filter life, increased dirt holding capacity and reduced maintenance costs.

Combination cyclone separator and cartridge filter in a single compact design

Patented Up-flow design with tangential entry - prevents air entrapment

Rotational flow "flutters" media pleats - improving loading performance

Electropolished 304 stainless steel housing

Fail-Safe lid closure, rated for 150 psi

CPVC standpipe (standard) - stainless steel optional

Three sizes for greater media surface area

Extensive choice of cartridge micron ratings

and media, including carbon block

NSF 61 listed

[Ver PDF](#)

INFORMACIÓN ADICIONAL

COTECNO