

HARMSCO HOUSING HP HUR 40 HP FILTER HOUSING



SKU: HP HUR 40 HP PM | **Categorías:** [Equipo Analítico](#) |

DESCRIPCIÓN DEL PRODUCTO

HARMSCO HOUSING HP HUR 40 HP FILTER HOUSING

Part Number: HP HUR 40 HP PM



Especificaciones

Marca	Harmsco Housing HP
Tipo	for Poly-Mesh Cartridge
Presión de trabajo bar	10.3
Presión psi	150
Temperatura máxima de °C	60
Temperatura máxima de °F	140
Área de medios ft ²	40
Flujo gpm	50
Flujo l/min	up to 189
Flujo m ³ /h	up to 12
Conexión de drenaje - pulgadas	1 NPT
Material	304 Stainless Steel
O-Ring / juntas /	EPDM

Dimensiones / Pesos

Entrada inch	2
Salida pulgadas	2
Longitud del cartucho inch	9-5/8
diámetro exterior pulgada	Ø7-3/4
Altura pulgadas	19-1/2
Peso kg	18.2
Peso lb	40
Cantidad por caja	1 piezas
Aplicación	Drinking water, Process water, Industrial water, RO Pre-Filtration, Coolig Tower, Surface water



Lower Operation Cost

Harmsco® HP Hurricane® filters provide unsurpassed performance.

Our unique design separates dense solids prior to cartridge filtration for extended filter life, increased dirt holding capacity and reduced maintenance costs.

Combination cyclone separator and cartridge filter in a single compact design

Patented Up-flow design with tangential entry - prevents air entrapment

Rotational flow "flutters" media pleats - improving loading performance

Electropolished 304 stainless steel housing

Fail-Safe lid closure, rated for 150 psi

CPVC standpipe (standard) - stainless steel optional

Three sizes for greater media surface area

Extensive choice of cartridge micron ratings

and media, including carbon block

NSF 61 listed

[Ver PDF](#)

INFORMACIÓN ADICIONAL

COTECNO