

## HARMSCO HOUSING HP HUR 90 HP FILTER HOUSING



**SKU:** HP HUR 90 HP HT | **Categorías:** [Equipo Analítico](#) |

## DESCRIPCIÓN DEL PRODUCTO

### HARMSCO HOUSING HP HUR 90 HP FILTER HOUSING

Part Number: HP HUR 90 HP HT



#### Especificaciones

Marca	Harmsco Housing HP
Tipo	for Hight Temprature Cartridge
Presión de trabajo bar	10.3
Presión psi	150
Temperatura máxima de °C	60
Temperatura máxima de °F	140
Área de medios ft <sup>2</sup>	90
Flujo gpm	100
Flujo l/min	up to 378
Flujo m <sup>3</sup> /h	up to 24
Conexión de drenaje - pulgadas	1 NPT
Material	304 Stainless Steel
O-Ring / juntas /	EPDM

#### Dimensiones / Pesos

Entrada inch	2
Salida pulgadas	2
Longitud del cartucho inch	19-1/2
diámetro exterior pulgada	Ø7-3/4
Altura pulgadas	29-7/8
Peso kg	24
Peso lb	52
Cantidad por caja	1 piezas
Aplicación	Drinking water, Process water, Industrial water, RO Pre-Filtration, Coolig Tower, Surface water



#### Lower Operation Cost

Harmsco® HP Hurricane® filters provide unsurpassed performance.

Our unique design separates dense solids prior to cartridge filtration for extended filter life, increased dirt holding capacity and reduced maintenance costs.

Combination cyclone separator and cartridge filter in a single compact design

Patented Up-flow design with tangential entry - prevents air entrapment

Rotational flow "flutters" media pleats - improving loading performance

Electropolished 304 stainless steel housing

Fail-Safe lid closure, rated for 150 psi

CPVC standpipe (standard) - stainless steel optional

Three sizes for greater media surface area

Extensive choice of cartridge micron ratings

and media, including carbon block

NSF 61 listed

[Ver PDF](#)

## INFORMACIÓN ADICIONAL

COTECNO