

HARMSCO HOUSING WB 40SC-1 WATERBETTER FILTER HOUSING



SKU: WB 40SC-1 | **Categorías:** [Equipo Analítico](#) |

DESCRIPCIÓN DEL PRODUCTO

HARMSCO HOUSING WB 40SC-1 WATERBETTER FILTER HOUSING

Part Number: WB 40SC-1



Especificaciones

Marca	Harmsco Housing WB
Presión de trabajo bar	10.3
Presión psi	150
Temperatura máxima de °C	60
Temperatura máxima de °F	140
Flujo gpm	up to 2400
Conexión de drenaje - pulgadas	1 NPT
Material	304 Stainless Steel
O-Ring / juntas /	EPDM
Tipo de Cierre	Wing nuts

Dimensiones / Pesos

Entrada inch	1 NPT
Salida pulgadas	1 NPT

Diámetro en pulgadas	Ø13
Altura pulgadas	19-1/4
Peso kg	18.2
Peso lb	40
Aplicación	Drinking water, Process water, Industrial water, Cooling water, RO Pre-Filtration, Utility water



Harmsco® WB WaterBetter® single-cartridge filters deliver high flow, extended filter life, increased dirt holding capacity and ease of operation.

- Patented Up-flow design
- CPVC standpipe (standard) - stainless steel optional
- Three sizes for greater media surface area
- Reduced installation cost
- Simple alternative to complex multiple cartridge housings
- Electropolished 304 stainless steel housing
- Fail Safe closure system
- Extensive choice of cartridge micron ratings and media, including carbon block

[Ver PDF](#)

INFORMACIÓN ADICIONAL

COTECNO