



HARMSCO HSB -2-2-STD PE-15-G2PS-SA LIQUID FILTER BAG



SKU: HSB PE-15-G2PS-SA STD | **Categorías:** [Equipo Analítico](#) |



DESCRIPCIÓN DEL PRODUCTO

HARMSCO HSB -2-2-STD PE-15-G2PS-SA LIQUID FILTER BAG

Part Number: HSB PE-15-G2PS-SA STD



Especificaciones

Marca	Harmsco HSB
Micrón	15
Temperatura máxima de °C	135
Temperatura máxima de °F	275
Flujo gpm	200
Material	Polyester
Intervalo de pH	3-11

Dimensiones / Pesos

Longitud en pulgadas	32
diámetro exterior pulgada	Ø7.06
Cantidad por caja	50 pieces



Harmsco Filtration

Harmsco was founded in 1958 by John Harms soon after he and his family relocated to Florida from the State of Ohio. At the time the company's primary assets were John's experience in the liquid filtration industry, his unique Up-Flow filter design, wife Laura's trustworthy assistance and John's resolve to manufacture high quality filtration equipment and market them worldwide.

Harmsco Up-Flow Cartridge Filters were patented and introduced to the market in 1968. Almost immediately, people in the filtration industry took note of the many advantages Harmsco Filters provide.

As a result, sales began to accelerate.

Features / Benefits

- High rejection rates
- High flow rates
- Superior quality and costs savings
- Reduced waste disposal
- Low pressure drop

Functionality

- high purity chemicals
- bottled water
- pharmaceuticals, cosmetics
- Sea water
- Ultra Pure water

Typical Applications

- Reverse Osmosis Pre-filtration
- Drinking water
- Desalination Pre-filtration
- Cooling Tower Filtration
- Chill Water Loop Filtration
- Food & Beverage Filtration
- Marine / Aquatic Filtration
- Coolants
- Bottled water
- Organic solvents

[Ver PDF](#)



INFORMACIÓN ADICIONAL

COTECNO