

## MUESTRA



SKU: N / A | Categorías: [Dispositivos varios](#) |

## DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] template [/vc_column_text] [vc_row_inner column_margin="default" text_align="left" css=".vc_custom_1597668708409 {border-radius: 2px !important;}" ] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]
```

### Imagen

```
[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]
```

### Nombre del Producto

```
[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]
```

### Descripción corta

```
[/vc_column_text] [/vc_column_inner] [/vc_row_inner] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138363" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]
```

LED de pantalla de viento

4.3250.xx.0xx[/vc\_column\_text] [/vc\_column\_inner] [vc\_column\_inner column\_padding="no-extra-padding"]

```
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text] Indicador digital para la visualización de la velocidad y dirección del viento
para sensores con interfaces digitales. [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6"
button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento/"] [/vc_column_inner] [/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text]
```

#### LED de pantalla de viento

```
4.3251.xx.0xx [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text] template Instrumento de visualización digital que indica la velocidad y
dirección del viento con interfaces digitales.
```

- Versión de envío

```
[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-4/"] [/vc_column_inner] [/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text]
```

#### LED de pantalla de viento

```
4.3250.xx.1xx [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
```

column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/2" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"] [vc\_column\_text] Indicador digital para la visualización de la velocidad y dirección del viento para sensores con interfaces analógicas. [/vc\_column\_text] [nectar\_cta btn\_style="see-through" heading\_tag="h6" button\_color="default" link\_type="new\_tab" alignment="left" display="block" link\_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-2/"] [/vc\_column\_inner] [/vc\_row\_inner]

[vc\_row\_inner column\_margin="default" text\_align="left"] [vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"] [image\_with\_animation image\_url="138363" alignment="center" animation="Fade In" hover\_animation="none" border\_radius="none" box\_shadow="none" image\_loading="default" max\_width="100%" max\_width\_mobile="default"] [/vc\_column\_inner] [vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"] [vc\_column\_text]

#### LED de pantalla de viento

4.3251.xx.1xx [/vc\_column\_text] [/vc\_column\_inner] [vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/2" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"] [vc\_column\_text] Instrumento de visualización digital que indica la velocidad y la dirección del viento con interfaces analógicas.

- Versión de envío

[/vc\_column\_text] [nectar\_cta btn\_style="see-through" heading\_tag="h6" button\_color="default" link\_type="new\_tab" alignment="left" display="block" link\_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-5/"] [/vc\_column\_inner] [/vc\_row\_inner]

[/vc\_column] [/vc\_row]

## INFORMACIÓN ADICIONAL

COTECNO