

INTERFAZ DIGITAL DE COMPUTADORA PORTÁTIL PARA INSPECCIONES SEESNAKE®



SKU: N / A | **Categorías:** [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección por vídeo de desagüe y alcantarillado](#), [Inspección Y Localización](#), [Monitores y grabadoras](#) | **Etiquetas:** [Ridgid](#)

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]

Interfaz digital de computadora portátil para inspecciones SeeSnake®

Aproveche el poder y la flexibilidad de una computadora portátil con las cámaras y carretes de inspección de drenajes SeeSnake LT1000, SeeSnake Mini o Normal. Utilice una computadora portátil como unidad de control de la cámara para agregar potentes capacidades de monitoreo, grabación, almacenamiento y comunicaciones.

[vc_column_text][vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]

[vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section][vc_column][vc_row]

COTECNO