

LOCALIZADOR NAVITRACK SCOUT®



SKU: N / A | **Categorías:** [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Localización de tubería sanitaria](#) | **Etiquetas:** [Ridgid](#)

DESCRIPCIÓN DEL PRODUCTO

Localizador NaviTrack Scout®

El localizador NaviTrack Scout se diseñó para resolver las localizaciones de transmisor remoto (sonda) más exigentes usando tecnología multidireccional de localización.

Localizaciones más sencillas

La tecnología de antena multidireccional del NaviTrack Scout siempre capta toda la señal. Simplemente, maximice la potencia de la señal y habrá encontrado el objetivo. Sin ceros ni falsos picos que compliquen la localización.

Precisión

Este dispositivo verifica la posición de la localización usando una pantalla de microcartografía para señalar polos característicos al frente y detrás del objetivo, lo que asegura una localización precisa.

Profundidad automática

La profundidad se calcula y muestra automáticamente cuando se está sobre el objetivo.

```
[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]
```

```
[/vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section][/vc_column][vc_row]
```

COTECNO