

LOCALIZADOR SEEKTECH SR-20



SKU: N / A | **Categorías:** [cañerías](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Servicios públicos](#), [tuberías y vacíos](#) | **Etiquetas:** [Ridgid](#)

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

Localizador SeekTech SR-20

Un receptor liviano, pero resistente, que le ofrece toda la información necesaria para lograr localizaciones más rápidas y exactas.

[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]

[/vc_column][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section][/vc_column][vc_row]

COTECNO