

TRANSMISOR DE CONDUCTOS SEEKTECH ST-305



SKU: N / A | **Categorías:** [cañerías](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Servicios públicos](#), [tuberías y vacíos](#) | **Etiquetas:** [Ridgid](#)

DESCRIPCIÓN DEL PRODUCTO

Transmisor de conductos SeekTech ST-305

El transmisor de línea SeekTech ST-305 de 5 W le permite activar líneas metálicas para su localización.

```
[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]
```

```
[/vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]  
[tabbed_section style="default" alignment="left"]  
[/tabbed_section][/vc_column][vc_row]
```

COTECNO