

PEQUEÑOS TRANSMISORES DE VIENTO



SKU: N / A | **Categorías:** [Thies Clima](#), [Viento](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Los pequeños transmisores de viento son transmisores de medición ideales con la mejor relación precio / rendimiento para los requisitos estándar.

Las aplicaciones típicas son:

- Técnica de
- Control Sistema de control de edificios

[/vc_column_text] [vc_row_inner column_margin="default" text_align="left" css=".vc_custom_1597668708409 {border-radius: 2px !important;}"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Imagen

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Nombre del Producto

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Descripción corta

[/vc_column_text] [/vc_column_inner] [/vc_row_inner] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138447" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"] [vc_column_text]

bg_image_animation="none"] [vc_column_text] Transmisor de dirección del viento

4.3124.30.018 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de dirección del viento pequeño con salida de potenciómetro [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-3/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138447" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de dirección del viento

4.3127.40.000 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de dirección de viento pequeño con contactos reed [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-4/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138450" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de dirección del viento

4.3140.51.010 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

```
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[vc_column_text]Transmisor de dirección del viento pequeño con salida de
potenciómetro[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default"
link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-de-direccion-del-viento-5/"][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][[vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[image_with_animation image_url="138454" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[vc_column_text]
```

Transmisor de viento combinado

```
4.3329.00.510[[vc_column_text]][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[vc_column_text]Transmisor de medida para medir la velocidad del viento, la dirección del
viento y la temperatura del aire.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6"
button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-7/"][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][[vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[image_with_animation image_url="138442" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[vc_column_text]
```

Transmisor de viento pequeño

```
4.3515.30.000[[vc_column_text]][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][[vc_column_text]Transmisores de velocidad de viento pequeños con reed -
contacto[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default"
```

link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-pequeno/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138445" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de viento pequeño

4.3515.5x.x61 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisores de velocidad de viento pequeños con salida analógica 0 ... 10 V [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-pequeno-2/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138445" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de viento pequeño

4.3515.5x.xxx [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisores de velocidad del viento pequeños con salida de frecuencia [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-pequeno-3/"] [/vc_column_inner] [/vc_row_inner]

COTECNO

COTECNO